




1

PRODUCT NUMBER	SERIES NAME	PITCH
20020316-GXXXXXXLF	21-500	5.00 mm




SECTION P-P

N=NUMBER OF POLES

Dim A	$N \times 5.0 [.197]$
Dim B	$(N-1) \times 5.0 [.197]$




POLES	TOLERANCE
2p-6p	$\pm 0.15 [.006]$
7p-12p	$\pm 0.25 [.010]$
13p-16p	$\pm 0.35 [.014]$
17p-24p	$\pm 0.40 [.016]$



P.C.B LAYOUT

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection MM INCH	product family TERMINAL BLOCK
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
H					angles X $\pm 0.5 [.020]$ X.X $\pm 0.3 [.012]$ X $\pm 1^\circ$ X.XX $\pm 0.1 [.004]$	scale	TERMINAL BLOCK FIXED HORIZONTAL WIRE INLET
			dr	BEER FU	062509		dwg no
			enr	BEER FU	062509		sheet 2 of 3
			chr	GARY HSIEH	062509		size
			appd	JOSEPH HSIA	062509		A4
sheet index	revision sheet						type
							CUSTOMER Drawing

PRODUCT NUMBER	SERIES NAME	PITCH
20020316-HXXXXXXLF	21-508	5.08 mm




SECTION P-P

N=NUMBER OF POLES

Dim A	N*5.08[.200]
Dim B	(N-1)*5.08[.200]

POLES	TOLERANCE
2p-6p	±0.15[.006]
7p-12p	±0.25[.010]
13p-16p	±0.35[.014]
17p-24p	±0.40[.016]



P.C.B LAYOUT

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection MM INCH	product family TERMINAL BLOCK
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
H					angles X±0.5[.020] X.X±0.3[.012] X°±1° X.XX±0.1[.004]	scale	TERMINAL BLOCK FIXED HORIZONTAL WIRE INLET
			dr	BEER FU	062509	FCI	dwg no
			enr	BEER FU	062509		sheet 3 of 3
			chr	GARY HSIEH	062509		size
			appd	JOSEPH HSIA	062509		A4
sheet index	revision	sheet				type	CUSTOMER Drawing