




Fig. 1

- Series 3XX are available with straight and right angle solder tails.
- Series 350 & 399...009 use MM #3404 and #5011 pins. See pages 179 & 181 for details.
- Series 301, 310 & 399...003 use MM #0156, #1001 & #1103 receptacles. See pages 136 & 137 for details.
- Receptacles use Hi-Rel, 4 finger #30 BeCu contact rated at 3 amps. See page 218 for details.
- Insulators are high temp. thermoplastic.





Fig. 2




Fig. 3




Fig. 4




Fig. 5

Ordering Information

Fig. 1	Series 350...006		Straight Pin Header						
	350-XX-1__-00-006000 Specify # of pins  01-64								
Fig. 2	Series 399...009		Right Angle Pin Header						
	399-XX-1__-10-009000 Specify # of pins  02-64								
For Electrical, Mechanical & Environmental Data, See pg. 4  XX=Plating Code See Below For RoHS compliance select  plating code.									
SPECIFY PLATING CODE XX=			10 	90	40 				
Pin Plating 			10μ" Au	200μ" Sn/Pb	200μ" Sn				
Fig. 3	Series 310...001		Straight Socket						
	310-XX-1__-41-001000 Specify # of pins  01-64								
Fig. 4	Series 301...056		Socket w/ Retention Pegs						
	301-XX-1__-41-560000 Specify # of pins  01-64								
Fig. 5	Series 399...003		Right Angle Socket						
	399-XX-1__-10-003000 Specify # of pins  01-64								
For Electrical, Mechanical & Environmental Data, See pg. 4  XX=Plating Code See Below For RoHS compliance select  plating code.									
SPECIFY PLATING CODE XX=			13 	91	93	99	41 	43 	44 
Sleeve (Pin) 			10μ" Au	200μ" Sn/Pb	200μ" Sn/Pb	200μ" Sn/Pb	200μ" Sn	200μ" Sn	200μ" Sn
Contact (Clip) 			30μ" Au	10μ" Au	30μ" Au	200μ" Sn/Pb	10μ" Au	30μ" Au	200μ" Sn