

NX8045GB

For OA / AV

■ Features

A small surface-mount type crystal unit.

- Compact and thin. (8.0×4.5×1.8mm)
- Supports low frequencies(from 4MHz).
- Ideal for OA/AV applications and Accessories for a car.
- Excellent environmental performance, including heat and shock resistance.
- Meets the requirements for re-flow profiling using lead-free solder.





■ Specifications

| Item Model | NX8045GB | | | | | | |
|---|---|---------------|--------------|------------------------|---------------|---------------------------------------|------------------------|
| Standard | Standard | | | | | Optional | |
| Nominal Frequency (MHz) | 4 ≤ F ≤ 4.9 | 5 ≤ F ≤ 7.499 | 7.5 ≤ F ≤ 40 | 4 ≤ F ≤ 4.9 | 5 ≤ F ≤ 7.499 | 7.5 ≤ F ≤ 48 | 4 ≤ F ≤ 48 |
| Overtone Order | Fundamental | | | | | Fundamental | |
| Frequency Tolerance (25 ±3 °C) | ±30 × 10 ⁻⁶ | | | ±20 × 10 ⁻⁶ | | | ±20 × 10 ⁻⁶ |
| Frequency versus Temperature Characteristics (with reference to +25 °C) | ±50 × 10 ⁻⁶ | | | ±30 × 10 ⁻⁶ | | | ±30 × 10 ⁻⁶ |
| Operating Temperature Range (°C) | -40 to +85 | | | −10 to +70 | | | -40 to +85 *2 |
| Storage Temperature Range (°C) | -40 to +125 | | | -40 to +85 | | | -40 to +125 *2 |
| Equivalent Series Resistance | Refer to *1 | | | | | Refer to *1 | |
| Level of Drive (µW) | 50 (Max. 500) | | | | | 50 (Max. 500) | |
| Load Capacitance (pF) | 8 | | | | | 6 to 32 | |
| Frequency Aging (+25 °C) | | | | | | Max. ±10 × 10 ⁻⁶ / year *2 | |
| Specifications Number | STD-CJL-5 STD-CSF-5 STD-CSF-6 STD-CJL-2 STD-CSF-3 STD-CSF-4 | | | | Refer to *3 | | |

Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.


- *2 If you have any other requests, NDK will study it.
- *3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.
 - Ex. Model, Frequency (24.000000MHz 6digits), S1: Fundamental or S3: 3rd overtone
 - Operating Temperature Range (-40 to +85°C) Frequency versus Temperature Characteristics (±30 × 10-6)
 - Frequency Tolerance (±20 × 10⁻⁶) Load Capacitance (10pF)

NX8045GB

24.000000MHz

S1-4085-30-20-10

■ Dimensions



*1 Equivalent Series Resistance

| Nominal Frequency (MHz) | Equivalent Series Resistance Max. (Ω) | | | |
|----------------------------|--|--|--|--|
| 4 ≤ F < 5 | 300 | | | |
| 5≤F<8 | 250 | | | |
| 8 ≤ F < 9.5 | 200 | | | |
| 9.5 ≤ F < 10 | 120 | | | |
| 10 ≤ F < 12 | 100 | | | |
| 12 ≤ F < 13 | 80 | | | |
| 13 ≤ F ≤ 40 | 50 | | | |

If you have any other requests, NDK will study it.