




Fig. 1




Fig. 2





Fig. 3

- Series 351 Interconnect header strips come in three lengths with 0,46 dia. pluggable solder tails at one end and 0,64 dia. pins at the other, see series:
351...003 uses pin #5503
351...004 uses pin #5504
351...005 uses pin #5505
- 0,46 pluggable solder tails are available at both ends, please see series:
351...009 uses pin #5509
351...010 uses pin #5510
351...011 uses pin #5511
See pages 179 & 181 for details.
- Insulators are high temp. thermoplastic.



Ordering Information

Fig. 1	Series 351...003	0,46 / 0,64	Solder Tails
	351-10-1__-00-003000		
	Specify # of pins	01-64	
	Series 351...009	0,46 / 0,46	Solder Tails
Fig. 2	351-10-1__-00-009000		
	Specify # of pins	01-64	
	Series 351...004	0,46 / 0,64	Solder Tails
	351-10-1__-00-004000		
Fig. 3	Specify # of pins	01-64	
	Series 351...010	0,46 / 0,46	Solder Tails
	351-10-1__-00-010000		
	Specify # of pins	01-64	
Fig. 3	Series 351...005	0,46 / 0,64	Solder Tails
	351-10-1__-00-005000		
	Specify # of pins	01-64	
	Series 351...011	0,46 / 0,46	Solder Tails
Fig. 3	351-10-1__-00-011000		
	Specify # of pins	01-64	

For Electrical,
Mechanical & Environmental
Data, See pg. 4

For RoHS compliance
select plating code.

PLATING CODE XX=	10			
Pin Plating	0,25μ Au			