




NOTES:

1. METAL SHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0; GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. NO CONTACTS ON POS. A1 + A2
5. THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
6. COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
7. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.L.B
8. CONNECTOR IS PART MARKED: **3027W2SAM99A30X CONEC ABC**

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 2:1 (5:1)	
							material: SEE NOTES	
					date	name	title: D-SUB COMBINATION FEMALE 27W2S SOLDER CUP with threaded insert	
				drawn	15.04.15	Henneboel		
				appd.	15.04.15	Lehmenkühler		
				norm				
				d-old			dwg no: 13K1A4948	
	a	Original					DIN-A3	
	rev.	description	date	name			sh: 1	
						part no: 3027W2SAM99A30X		

CONEC