

HDC CM BUS SV GCA F**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The ConCept-CSB module is a double module and takes up two slots in the ConCept module frame. The ConCept-CSB module consists of a module carrier that is capable of holding two contact carriers. The contact carrier is manufactured with a die-cast zinc alloy which provides it with excellent shielding capabilities. The crimp contacts are insulated from the contact carrier and mounted in a plastic insert. A variety of pole counts – 1, 4 and 8 poles – are available to ensure compatibility with a wide range of applications.

General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	1983820000
Type	HDC CM BUS SV GCA F
GTIN (EAN)	4032248688951
Qty.	1 pc(s).

HDC CM BUS SV GCA F

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	3.9 mm	Height (inches)	0.154 inch
Width	21.5 mm	Width (inches)	0.846 inch
Length	33.5 mm	Length (inches)	1.319 inch
Net weight	8.8 g		

Temperatures

Limit temperature	-40 °C ... 70 °C
-------------------	------------------

ConCept Pneumatic module

Colour	Silver grey	UL 94 flammability rating	V-0
--------	-------------	---------------------------	-----

Dimensions

Height of socket	3.9 mm	Total length base	33.5 mm
Width	21.5 mm		

General data

Material	Polycarbonate	Series	ConCept module
Type	Earth connection clamp	UL 94 flammability rating	V-0

Version

Material	Polycarbonate
----------	---------------

Classifications

ETIM 6.0	EC002312	ETIM 7.0	EC002312
ETIM 8.0	EC002312	ECLASS 9.0	27-44-02-92
ECLASS 9.1	27-44-02-18	ECLASS 10.0	27-44-02-92
ECLASS 11.0	27-44-02-92	ECLASS 12.0	27-44-02-92

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN