

										</					


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C200383	2020-03-28	Peng	B XI


SAMI2C-XXG03



- 01:MPQ(1000PCS)/REEL
- 02:LOOSE PIECE 500PCS
- 03:LOOSE PIECE 100PCS




SECTION A-A



SECTION B-B

Note:

- * Material
 - Contact Body: Copper Alloy
 - Outer Spring: Stainless steel
- * Contact Finish: 3u"Min Gold Plating
- * Current Rating: 20A Max
- * Termination Type: Crimping
- * Wire Range: 14AWG~12AWG
- * Salt Spray Test 48H
- * This drawing is supplied for information only design features specifications and performance data



UNIT:mm				TITLE 20A MALE CLAW PIN TERMINAL			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Jinhai		DATE 2015-08-11					
TOLERANCE ±0.5				SCALE 5:2					SIZE A4		SHEET 1 OF 1		DWG NO SAMI2C-XXG03		CHECKED BY Rensong		DATE 2015-08-11	
				REV. B					WC-REV. A.3		QC:Inspection item		CUSTOMER ALTW		APPROVED BY Jerry		DATE 2015-08-11	

Amphenol LTW
安費諾亮泰企業股份有限公司