

SERIES

9405R & 9406R
9405 & 9406



Tunable Variable RF Coils

Leads AWG #24 Tinned Copperweld

Tuning Torque 0.1 to 3.5 oz. in.

Pin #1 is identified by white dot on 9406 only.

Current Rating at 90°C Ambient 35°C Rise

Operating Temperature Range
-55°C to +125°C

Max. Power Dissipation at 90°C - 0.3 W

Weight Max. (Grams) 4.0

Units are electro-magnetically shielded

Core and Shield Material Ferrite

Ordering Information

Vertical Coil = Dash No. prefixed by 9405; Horizontal Coil = Dash No. prefixed by 9406. Additionally – an electrostatic shield for 9405 is available on a custom basis; order as 9415-XX

9405 Marking DEC; part number

9406 Marking Part number; DEC

Example: 9405R-10


DEC
9405R-10

Packaging Bulk only

Made in the U.S.A.

RF II									
</									

*Complete part # must include series # PLUS the dash #



Physical Parameters

Dimension	A	B	C	D	E	F	G	H	J	K, L
In.	0.200 ± 0.010	0.020 ± 0.0015	0.187 ± 0.020	0.500 max.	0.380 max.	0.400 ± 0.020	0.500 max.	0.300 ± 0.010	0.187 ± 0.020	0.375 max.
mm	5.08 ± 0.25	0.508 ± 0.038	4.75 ± 0.51	12.7 max.	9.65 max.	10.16 ± 0.51	12.7 max.	7.62 ± 0.25	4.75 ± 0.51	9.53 max.