



江苏长晶科技股份有限公司
JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD.

产 品 规 格 书

SPECIFICATIONS FOR PRODUCT

产品类型 TYPE : Crystal Resonator

产品规格 SPEC : 26MHz/2016/8PF/10PPM

产品型号 P/N : CJ16-260000810B20

日期 DATE : 2024/12/02

核准及签名

R&D APPR. SIGNATURED

拟制 ISSUE	审核 CHECK	批准 APPROVAL
Ivan 2024/12/02	Abbey 2024/12/02	Ken 2024/12/02

江 苏 长 晶 科 技 股 份 有 限 公 司

JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD.

地址：中国江苏省南京江北新区产业技术研创园江淼路88号腾飞大厦C座13楼

Add: 13Th Floor, C Block, Tengfei Building, No. 88 Jiangmiao Rd. Pukou

District, Nanjing City, Jiangsu Province, China

Specification Revision Record Sheet



SMCE2016 4 pads Crystal Resonator

CJ16-260000810B20

1. Scope:

- 1.1 This specification applies to the RoHS/HF compliance quartz crystal unit with a frequency of 26MHz which will be used in crystal resonator applications.

2. Construction:

- 2.1 Type of Quartz Resonator: SMCE2016 4pads

3. Electrical Characteristics

- | | |
|---|--------------------------|
| 3.1 Nominal Frequency(f): | 26MHz |
| 3.2 Load Capacitance(C_L): | 8pF |
| 3.3 Frequency Tolerance($\Delta f/f$): | ± 10 ppm |
| 3.4 Frequency Temperature Stability: | ± 20 ppm(Ref. @25°C) |
| 3.5 Resonance Resistance(ohm): | 50ohms Max |
| 3.6 Osc mode: | Fundamental mode |
| 3.7 Shunt Capacitance(C_0): | <2pF |
| 3.8 Drive Level(D_L): | <100μW |
| 3.9 Operating Temperature Range(T_{OPR}): | -40 to + 85°C |
| 3.10 Storage Temperature Range(T_{STG}): | -55 to + 125°C |
| 3.11 Insulation Resistance(IR): | >500 M ohms |
| 3.12 Aging(Δf_A): | ± 3 ppm per Year |

4. Reliability Specifications

This is the quality control and quality assurance and reliability tests performance data for the RoHS/HF compliance 26MHz SMCE2016 4pads crystal resonators related to the specification and approval sheet provided by JSCJ.


NO.	ITEM	SPECIFICATION	TEST METHOD
4.1	Free fall	$\Delta FL \leq \pm 5\text{ppm}$ $\Delta RR \leq \pm 5\Omega$ or 15%	Height: 100cm, Wooden block: 3cm, Dropping times: 3times
4.2	Vibration	$\Delta FL \leq \pm 5\text{ppm}$ $\Delta RR \leq \pm 5\Omega$ or 15%	Amplitude: 1.5mm, Frequency: 10~55Hz, Direction: X, Y, Z, Period: 2h
4.3	Resistance to soldering heat	$\Delta FL \leq \pm 5\text{ppm}$ $\Delta RR \leq \pm 5\Omega$ or 15%	Temperature: +260°C±5°C, Period: 10s±1s
4.4	High temp. and humidity	$\Delta FL \leq \pm 5\text{ppm}$ $\Delta RR \leq \pm 5\Omega$ or 15%	Temperature: 85°C±2°C, Humidity: 85%RH±3%RH, Period: 48h
4.5	Low temperature storage	$\Delta FL \leq \pm 5\text{ppm}$ $\Delta RR \leq \pm 5\Omega$ or 15%	Temperature: -40°C±2°C, Period: 2h
4.6	High temperature storage	$\Delta FL \leq \pm 5\text{ppm}$ $\Delta RR \leq \pm 5\Omega$ or 15%	Temperature: 125°C±2°C, Period: 16h
4.7	Temperature cycle	$\Delta FL \leq \pm 5\text{ppm}$ $\Delta RR \leq \pm 5\Omega$ or 15%	1cycle: -40°C(30min)→100°C(30min), 30cycle
4.8	Substrate Bending Test	$\Delta FL \leq \pm 5\text{ppm}$ $\Delta RR \leq \pm 5\Omega$ or 15%	Bend Amount: 3mm, Force: 10s by 0.5mm/s speed
4.9	Fine leak	Leakage values≤1.0E-9Pa	Helium leakage detector shall used to measure the leakage rate of gas through any faulty seal. Pressure: 500Kpa, duration: 2h
4.10	Weldability	Tin leaching rate≥95%	Temperature: +235°C±5°C, Period: 2s±0.2s
4.11	OTHERS		

Notes : The above test items and judgment standards are for reference only, and the actual reliability report shall prevail.

5. Recommended Reflow soldering condition (SMD)

Solder profile

Peak: $260 \pm 5^{\circ}\text{C}$ Soldering zone: 230°C or more, $30 \pm 10\text{s}$. Pre-heating zone 1: $150 \sim 180^{\circ}\text{C}$, $90 \pm 30\text{s}$




Temperature profile for reflow soldering


6. Soldering iron method

Bit temperature: $350 \pm 10^{\circ}\text{C}$ Application time of soldering iron: $3 \pm 1\text{s}$.

Package Outline Dimensions




Suggested Pad Layout




Marking


Procedure: Laser




For example:




Inside Structure



No.	Components	Materials
1	Package	Ceramic(Al_2O_3)
2	Lid	KV($\text{Fe}/\text{Ni}/\text{Co}$)
3	Crystal blank	SiO_2
4	Electrode	Ag、Cr
5	Silver glue	Resin、Ag




EMBOSED TYPE DIMENSIONS




USER FEED DIRECTION

Package

Inside package



Outside package



NOTICE

JSCJ reserve the right to make modifications,enhancements, improvements, corrections or other changes without further notice to any product herein.JSCJ does not assume any liability arising out of the application or use of any product described herein.