

D




C

B

A

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- THE NOTED DIMENSION APPLIES FROM THE BASIC DIMENSION (NOT THE POST CENTERLINE) TO THE SURFACE INDICATED.
- 0.000762[.000030] GOLD ON CONTACT AREA, 0.00254-0.00508[.000100-.000200] MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER 0.00127[.000050] NICKEL.
- HOUSING: LCP, COLOR-BLACK.
POSTS: COPPER ALLOY.
- 0.000762[.000030] GOLD ON CONTACT AREA, 0.00254-0.00508[.000100-.000200] MATTE TIN ON SOLDER TAIL, ALL OVER 0.00127[.000050] NICKEL.
- PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
M1		REVISED PER ECN-22-165406	20JUL2022	RK	MF



RECOMMENDED PCB LAYOUT
FOR USE WITH .008 THICK STENCIL

6	OBSOLETE	5	35.56 [1.400]	14	37.69 [1.484]	30	6-146130-4
6	OBSOLETE	5	33.02 [1.300]	13	35.15 [1.384]	28	6-146130-3
7	OBSOLETE	5	30.48 [1.200]	12	32.61 [1.284]	26	6-146130-2
7	OBSOLETE	5	27.94 [1.100]	11	30.07 [1.184]	24	6-146130-1
7	OBSOLETE	5	25.40 [1.000]	10	27.53 [1.084]	22	6-146130-0
7	OBSOLETE	5	22.86 [.900]	9	24.99 [.984]	20	5-146130-9
7	OBSOLETE	5	20.32 [.800]	8	22.45 [.884]	18	5-146130-8
7	OBSOLETE	5	17.78 [.700]	7	19.91 [.784]	16	5-146130-7
7	OBSOLETE	5	15.24 [.600]	6	17.37 [.684]	14	5-146130-6
7	OBSOLETE	5	12.70 [.500]	5	14.83 [.584]	12	5-146130-5
7	OBSOLETE	5	10.16 [.400]	4	12.29 [.484]	10	5-146130-4
7	OBSOLETE	5	7.62 [.300]	3	9.75 [.384]	8	5-146130-3
7	OBSOLETE	5	5.08 [.200]	2	7.21 [.284]	6	5-146130-2
7	OBSOLETE	5	2.54 [.100]	1	4.67 [.184]	4	5-146130-1
7	OBSOLETE	5	17.78 [.700]	7	19.91 [.784]	16	1-146130-8
7	OBSOLETE	5	5.08 [.200]	2	7.21 [.284]	6	1-146130-7
7	OBSOLETE	3	35.56 [1.400]	14	37.69 [1.484]	30	1-146130-4
7	OBSOLETE	3	33.02 [1.300]	13	35.15 [1.384]	28	1-146130-3
7	OBSOLETE	3	30.48 [1.200]	12	32.61 [1.284]	26	1-146130-2
7	OBSOLETE	3	27.94 [1.100]	11	30.07 [1.184]	24	1-146130-1
7	OBSOLETE	3	25.40 [1.000]	10	27.53 [1.084]	22	1-146130-0
7	OBSOLETE	3	22.86 [.900]	9	24.99 [.984]	20	146130-9
7	OBSOLETE	3	20.32 [.800]	8	22.45 [.884]	18	146130-8
7	OBSOLETE	3	17.78 [.700]	7	19.91 [.784]	16	146130-7
7	OBSOLETE	3	15.24 [.600]	6	17.37 [.684]	14	146130-6
7	OBSOLETE	3	12.70 [.500]	5	14.83 [.584]	12	146130-5
7	OBSOLETE	3	10.16 [.400]	4	12.29 [.484]	10	146130-4
7	OBSOLETE	3	7.62 [.300]	3	9.75 [.384]	8	146130-3
7	OBSOLETE	3	5.08 [.200]	2	7.21 [.284]	6	146130-2
7	OBSOLETE	3	2.54 [.100]	1	4.67 [.184]	4	146130-1

7 SUPERSEDED BY 6-146130-0

5	35.56 [1.400]	14	37.69 [1.484]	30	6-146130-4
5	33.02 [1.300]	13	35.15 [1.384]	28	6-146130-3
5	30.48 [1.200]	12	32.61 [1.284]	26	6-146130-2
5	27.94 [1.100]	11	30.07 [1.184]	24	6-146130-1
5	25.40 [1.000]	10	27.53 [1.084]	22	6-146130-0
5	22.86 [.900]	9	24.99 [.984]	20	5-146130-9
5	20.32 [.800]	8	22.45 [.884]	18	5-146130-8
5	17.78 [.700]	7	19.91 [.784]	16	5-146130-7
5	15.24 [.600]	6	17.37 [.684]	14	5-146130-6
5	12.70 [.500]	5	14.83 [.584]	12	5-146130-5
5	10.16 [.400]	4	12.29 [.484]	10	5-146130-4
5	7.62 [.300]	3	9.75 [.384]	8	5-146130-3
5	5.08 [.200]	2	7.21 [.284]	6	5-146130-2
5	2.54 [.100]	1	4.67 [.184]	4	5-146130-1
5	17.78 [.700]	7	19.91 [.784]	16	1-146130-8
5	5.08 [.200]	2	7.21 [.284]	6	1-146130-7
5	35.56 [1.400]	14	37.69 [1.484]	30	1-146130-4
5	33.02 [1.300]	13	35.15 [1.384]	28	1-146130-3
5	30.48 [1.200]	12	32.61 [1.284]	26	1-146130-2
5	27.94 [1.100]	11	30.07 [1.184]	24	1-146130-1
5	25.40 [1.000]	10	27.53 [1.084]	22	1-146130-0
5	22.86 [.900]	9	24.99 [.984]	20	146130-9
5	20.32 [.800]	8	22.45 [.884]	18	146130-8
5	17.78 [.700]	7	19.91 [.784]	16	146130-7
5	15.24 [.600]	6	17.37 [.684]	14	146130-6
5	12.70 [.500]	5	14.83 [.584]	12	146130-5
5	10.16 [.400]	4	12.29 [.484]	10	146130-4
5	7.62 [.300]	3	9.75 [.384]	8	146130-3
5	5.08 [.200]	2	7.21 [.284]	6	146130-2
5	2.54 [.100]	1	4.67 [.184]	4	146130-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.KNAUB 30-09-94	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK G. DUBNICZKI 30-09-94	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G. DUBNICZKI 30-09-94	SURFACE MOUNT HEADER ASSY, MOD II, B/A, VERT, DR, .100 X.100 CL, .025 SQ.POST	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13[.005] 4 PLC ± - ANGLES ± -		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO	
MATERIAL		APPLICATION SPEC	RESTRICTED TO	
FINISH SEE TABLE		WEIGHT 0.000000	A100779C=146130	
CUSTOMER DRAWING		SCALE 8:1	SHEET 1 OF 1 REV M1	