



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-18-012662	06AUG2018	JM	RB
	A1	REV PER ECO-18-016694	18OCT2018	JM	RB
	A2	REV PER ECR-21-101839	07APR2021	MK	BC


D



2320913-2
SCALE 2:1
KEY B




2320913-3
SCALE 2:1
KEY C




2320913-4
SCALE 2:1
KEY D

C




2320913-1 SHOWN
KEY A

B




SECTION A-A

A




SECTION A-A

COMPANY LOGO



SCALE 2:1



1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY

2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)

3 MATERIAL: SILICONE
COLOR: MARINE BLUE

4. RECOMMENDED WIRE DIAMETER RANGE IS 2.18 TO 3.67mm.

5. RECOMMENDED BACKSHELLS:

STRAIGHT EXIT

- A. 2292860-1 SMOOTH WIRE EXIT
B. 2292860-2 NC12/NW10 CONDUIT WIRE EXIT
C. 2292860-3 NC08/NW7.5 CONDUIT WIRE EXIT

90° EXIT

- D. 2302481-1 SMOOTH WIRE EXIT
E. 2302481-2 NC12/NW10 CONDUIT WIRE EXIT
F. 2302481-3 NC08/NW7.5 CONDUIT WIRE EXIT

6. RECOMMENDED SEAL PLUG: 776363-1

7. MATING CONNECTOR: 2320920-X.

D	ORANGE	2320913-4
C	PURPLE	2320913-3
B	BLUE	2320913-2
A	TAN	2320913-1
KEY	TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. MCNEAL 29SEP2017	TE Connectivity		
DIMENSIONS: mm		CHK R. BALTER 29SEP2017			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. BALTER 29SEP2017	NAME CAP ASSEMBLY, 2 POSITION, STD DIA SEAL, HIGH TEMP, AMPSEAL 16		
0 PLC ±		PRODUCT SPEC 108-32602	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
1 PLC ±		APPLICATION SPEC 114-32362	A200779C-2320913		
2 PLC ±0.30		WEIGHT 9g	SCALE 4:1 SHEET 1 OF 1 REV A2		
3 PLC ±		CUSTOMER DRAWING			
4 PLC ±					
ANGLES ±					
FINISH -					
-					