







RECOMMENDED PCB LAYOUT

Poles	Dim L	Dim B	Dim C	Dim D
2×2-2×5p	±0.15	±0.15	±0.15	±0.15
2×6-2×10p	±0.20	±0.20	±0.20	±0.20
2×11-2×15p	±0.25	±0.25	±0.25	±0.25
2×16-2×20p	±0.30	±0.30	±0.30	±0.30
2×21-2×24p	±0.35	±0.35	±0.35	±0.35

N = Number of poles
 Dim L=(N-1)×3.5+13.8
 Dim B=(N-1)×3.5
 Dim C=(N-1)×3.5+8.6
 Dim D=(N-1)×3.5



SIGN	DATE	DESCRIPTION	APPROVER
△	1/30'07	Soldering temperature changed from 245° to 250°	Tony
△	04/08'09	The current rating and operating temperature are changed	Jacke
△	04/08'09	Add UL standard	Jacke
△	2009.10.10	The design is changed from the round hole to hexagonal hole.	Jacke
△	07/05'11	Remove the "T" shape	Aaron
△	04/26'12	The Dimension Dim C is added	Chen Bo
△	04/26'12	Flange nut is changed	Chen Bo
△	04/26'12	Add the cutaway view	Chen Bo
△	04/26'12	The material is changed from Brass to Copper	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ③ Short contact pin: Copper, Tin plated
- Item ④ Long contact pin: Copper, Tin plated
- Item ⑤ Terminal(housing): Thermoplastic (UL94V-0)
- Item ⑥ With flange nut: Brass ,M2.5
- Item ⑦ Terminal(cover): Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 300V
- Current rating: 10A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:
- Critical dimension:

VO xx 1 2 x 1 xxxx G

No. OF POLES
 04: 2×2 POLES
 06: 2×3 POLES
 :
 48: 2×24 POLES

Color
 0 Black (RAL9005)
 2 Red (RAL3001/D)
 3 Orange(RAL2011/P)
 4 Yellow(RAL1018/A)
 5 Green(RAL6018/T)
 6 Blue (RAL5015/A)
 8 Grey(RAL7035/D)
 9 White(RAL1102)
 C Green(RAL6018/U)

G: RoHS compliant
 (lead<4%)
 In copper Alloy
 0000: "@" Logo (Standard)
 000A: "ANYTEK" Mark
 Any special item by
 customer request.
 please contact sales
 department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VO-3.50 Series 2×2P-2×24P Right angle (With flange)				
PART NO.	VOxx12x1xxxxG		DWG NO.	8V00003	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Chen Bo 04/26'12	Chen Bo 04/26'12		X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
SHEET: 01/01		UNIT: mm SCALE: NONE REV.: H			