




TE Internal #: 2355151-3
Automotive Seals & Cavity Plugs, Single Wire Seal, Cavity Diameter
.653 in [16.6 mm], Silicone, Excellent, 30 – 35, Contains Lubricant,
Blue
[View on TE.com >](#)

Connectors > Automotive Connectors > Automotive Seals & Cavity Plugs



Connector Seal Type: **Single Wire Seal**
Cavity Diameter: **16.6 mm [.653 in]**
Compatible Insulation Diameter Range: **20.1 – 20.9 mm [.791 – .823 in]**
Seal Material: **Silicone**
Resistance to Hydrocarbons: **Excellent**

Features

Product Type Features

Connector Seal Type	Single Wire Seal
---------------------	------------------

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Seal Material	Silicone
Primary Product Color	Blue

Housing Features

Centerline (Pitch)	40 mm[1.57 in]
--------------------	----------------

Dimensions

Cavity Diameter	16.6 mm[.653 in]
Compatible Insulation Diameter Range	20.1 – 20.9 mm[.791 – .823 in]

Usage Conditions

Operating Temperature (Max)	288 °C[140 °F]
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]



Other

Resistance to Hydrocarbons	Excellent
Shore A Hardness	30 – 35
Contains Lubricant	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 2371017-1 2POS,IPT,RING TONGUE HSG ASSY, SLD</p>	 <p>TE Part # 2355146-1 3POS,IPT,RING TONGUE HSG ASSY, SLD</p>	 <p>TE Part # 2355146-2 3POS,IPT,RING TONGUE HSG ASSY, SLD</p>	 <p>TE Part # 2371017-2 2POS,IPT,RING TONGUE HSG ASSY, SLD</p>
---	--	---	---



Documents

Product Drawings

SWS,COAX

English

CAD Files

Customer View Model

ENG_CVM_CVM_2355151-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2355151-3_A.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2355151-3_A.3d_igs.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English