







△ N = Number of poles

DimL=N×5.00±1.5
DimB=(N-1)×5.00

POLES	Dim L	Dim B
1p	±0.1	±0.15
2p-6p	±0.2	±0.15
7p-12p	±0.3	±0.25
13p-18p	±0.4	±0.35
19p-24p	±0.45	±0.4

SIGN	DATE	DESCRIPTION	APPROVER
△	1/31/07	The soldering temperature from 245° to 250°	Aaron
△	05/28/13	change the structure	Da cheng
△	05/28/13	update the drawing	Da cheng
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item ① Insulator body: Thermoplastic (UL94V-0)
- Item ② Insulating cover :Thermoplastic (UL94V-0)
- Item ③ Contact pin : Brass.Tin plated
- Item ④ Wire guard: Stainless steel

Electrical:

cULus

- Voltage rating: 250V

- Current rating: 8A

- Wire range: 12-28

- Solid wire(AWG): 12-28

- Stranded wire(AWG): 12-28

- Wire strip length: 8-9mm

- Withstanding Voltage: 15KV

- Operating temperature: -40°C to +115°C

- △△ Soldering temperature: 260°C±5°C/5 Sec

- Safety Approval: cULus

- △ Critical dimension: ∇

HM XX 50 x 0 xxxx G

No. OF POLES ———→ △ Roh's compliant (lead<4%) In copper Alloy

01: 1 POLES ———→ △ COLOR 0000 Standard @ Logo
02: 2 POLES ———→ 0 Black (RAL9005) 000A Standard ANY Logo
2 Red (RAL3001/D) Any special item by customer request,
3 Orange(RAL2011/P) please contact sales department.
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL 7004/P)
9 White(RAL1102)
C Multiple colors

24: 24 POLES

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HM 5.08mm Series Dip solder	
PART NO.	HMxx50x0xxxxG	DWG NO.	8HM0101
APPROVED	CHECKED	DESIGNED	DRAWN
	Da cheng 2013.05.28	Da cheng 2013.05.28	
		CUST NO.	
		UNIT: mm	X.X ±0.50
		SCALE: NONE	X.XX ±0.30
		SHEET: 01/01	REV.: E X° ±1°