



N=Number of poles
Dimension A&B&C

DIM A	$(N+1) \times 8.25$
DIM B	$(N-1) \times 8.25$
DIM C	$(N+2) \times 8.25 + 2.5$

Poles	Tolerance
2p-5p	$+0.25/-0.25$
6p-10p	$+0.35/-0.35$
11p-18p	$+0.40/-0.40$
19p-30p	$+0.50/-0.50$

SIGN	DATE	DESCRIPTION	APPROVER
△	2/06'06	Part No. changed	Tony
△	3/10'09	Structure changed	Seamus
△	3/10'09	Dimension changed	Seamus
△	11/03'12	Change the screw plating specification	Jacky
△	11/03'12	Change the dimensional tolerance	Jacky
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

MATERIALS ELECTRICAL

RATED VOLTAGE & CURRENT:

WITHSTAND VOLTAGE:

INSULATION RESISTANCE:

OPERATING TEMPERATURE RANG:

SCREW TORQUE VALUE:

WIRE RANGE:

1) MOLDED PARTS:

2) TERMINAL:

4 3) TERMINAL SCREWS:

APPROVAL: 

△ PART NO.:

Critical dimension:

YK 413 xx 3 x x 00G

NO. OF POLES

02: 2 POLES

03: 3 POLES
04: 4 POLES

04: 4 POLES

•

•

•

30: 30 POLES

300 V, 20 A

AC 2000 V/Min

1000 M Ω OR MORE AT DC 500 V

-40 °C ~ +115 °C

8.8 Lb-In.

22 - 12 AWG

POLYIMIDE 66, UL 94 V-0 BLACK

BRASS, 0.8t, Tin PLATED

STEEL, M3

RoHS compliant
(lead<4%) In copper Alloy

— MARK

0: "@" MARK

1: "ANY" MARK

— TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F

△ 1: TERMINAL: G/F, SCREW: Zin

2: TERMINAL: S_n, SCREW: G/F

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YK-413 With Flange Series						
PART NO.	YK413xx3xx00G			DWG NO.	8YK0002-413		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Jacky 2012.11.03	Jacky 2012.11.03		UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
				SHEET: 01/01	REV.: E	X.XX	±0.10
						X°	±1°