




PRODUCT NUMBER: 1636-0-57-15-00-00-03-0

www.mill-max.com  
DATA SHEET

1636-X-XX-15-00-00-03-0											
Low profile Target Discs, surface mount											
	<table border="1"><thead><tr><th>Basic Part Number</th><th>Target Disc Height (A)</th></tr></thead><tbody><tr><td>1636-0</td><td>.025" [0.64]</td></tr><tr><td>1636-1</td><td>.035" [0.89]</td></tr><tr><td>1636-2</td><td>.045" [1.14]</td></tr><tr><td>1636-3</td><td>.055" [1.40]</td></tr></tbody></table>	Basic Part Number	Target Disc Height (A)	1636-0	.025" [0.64]	1636-1	.035" [0.89]	1636-2	.045" [1.14]	1636-3	.055" [1.40]
Basic Part Number	Target Disc Height (A)										
1636-0	.025" [0.64]										
1636-1	.035" [0.89]										
1636-2	.045" [1.14]										
1636-3	.055" [1.40]										
	<small>Units: inch [mm] Standard Tolerances: Lengths: <math>\pm .005</math> [0.127] Diameters: <math>\pm .002</math> [0.051] Angles: <math>\pm 2^\circ</math></small>										



## 1636-0-57-15-00-00-03-0 SPECIFICATIONS


General Info		Materials	Technical Specs
Description <sup>1</sup> :	Spring-Loaded Target Contact with Flat Face	Shell Material <sup>4</sup> : Brass Alloy	Operating Temperature Range <sup>6</sup> : - 55/+125° C
Mounting Feature:	Surface Mount	Shell Plating <sup>5</sup> : 10 $\mu$ " Gold over Nickel	Current Rating <sup>7</sup> : Application Specific
Packaging:	Vertically on Tape & Reel		
RoHS <sup>2</sup> :	Yes		
Product Lifecycle <sup>3</sup> :	Active		

## NOTES:


1. Standard Tolerances:  
Lengths +/- .005" (0,13)  
Diameters: +/- .002" (0,051)  
Angles: +/- 2°
2. Mill-Max products labeled with the RoHS symbol are compliant with all three ROHS Directives. All of our products previously described as RoHS (2002/95/EC) and RoHS-2 (2011/65/EC) are also compliant with RoHS-3 (2015/863/EU).
3. Part is Active and in Production, No Scheduled Obsolescence
4. Brass Alloy 360 per ASTM B 16, or 385 per ASTM B455
5. GOLD per ASTM B 488, Type 1 (99.7% min. gold), Code C (130-200 HK {Knoop hardness}), NICKEL per ASTM B 689, Type 2 (Bright)
6. Per IEC 60512-11-(4,-9,-10,-12)
7. Current rating is typically a measured function of the female socket/connector. The amount of current a solid, male, brass pin can tolerate is a direct relation of the heat displaced based on current and the ability of neighboring components to handle displaced heat.

## ADDITIONAL PARTS, PACKAGING, & ASSEMBLY INFO

### Suggested P.C.B. Footprint



### 1636-X-57 Tape & Reel Details



## ADDITIONAL NOTES AND SPECIFICATIONS

In the interest of improved design, quality and performance, Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

## RELATED LINKS AND DOCUMENTS

Engineering Notebook: (<https://www.mill-max.com/engineering-notebooks/spring-loaded-pin-applications>)

Environmental Compliance: (<https://www.mill-max.com/rohs>)