




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-18-012662	08AUG2018	JM	RB
	A1	REV PER ECO-18-016694	18OCT2018	JM	RB




2320926-2
SCALE 2:1
KEY B




2320926-3
SCALE 2:1
KEY C




2320926-4
SCALE 2:1
KEY D




2320926-1 SHOWN
KEY A



SECTION A-A



SECTION A-A
WITH TPA IN CLOSED POSITION



- COMPANY LOGO
- SCALE 2:1
- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY
 - 2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)
 - 3 MATERIAL: SILICONE
COLOR: LT GRAY.
4. RECOMMENDED WIRE DIAMETER RANGE IS 1.30 TO 2.54mm.
5. RECOMMENDED BACKSHELLS:
- STRAIGHT EXIT
- A. 2292860-1 SMOOTH WIRE EXIT
 - B. 2292860-2 NC12/NW10 CONDUIT WIRE EXIT
 - C. 2292860-3 NC08/NW7.5 CONDUIT WIRE EXIT
- 90° EXIT
- D. 2302481-1 SMOOTH WIRE EXIT
 - E. 2302481-2 NC12/NW10 CONDUIT WIRE EXIT
 - F. 2302481-3 NC08/NW7.5 CONDUIT WIRE EXIT
6. RECOMMENDED SEAL PLUG: 776363-1.
7. MATING CONNECTOR: 2320932-X.

ORANGE	2320926-4
PURPLE	2320926-3
BLUE	2320926-2
TAN	2320926-1
TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±0.30
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

MATERIAL

-

DWN J MCNEAL 09OCT2017

CHK R BALTER 09OCT2017

APVD R BALTER 09OCT2017

PRODUCT SPEC 108-2184

APPLICATION SPEC 114-13065

WEIGHT 9g

Customer Drawing

TE Connectivity

NAME

CAP ASSEMBLY, 2 POSITION,
REDUCED DIA SEAL, HIGH TEMP,
AMPSEAL 16

SIZE A2

CAGE CODE 00779

DRAWING NO C-2320926

RESTRICTED TO -

SCALE 4:1

SHEET 1

OF 1

REV A1