

INTERCONNECTS

SERIES 416 • 2,54 GRID ELEVATED • DOUBLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3




FIG. 4




FIG. 5

- Elevated socket strips are available in 5 different heights:

416...006 uses pin # 0153-1

416...003 uses pin # 0153-2

416...007 uses pin # 0153-3


416...008 uses pin # 0153-4

416...001 uses pin # 0153-5

See page 167 for details

- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details

- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 416...006	Standoff Height = 5,99		
	416-XX-2	-41-006000		
	Specify number of pins	04-64		
FIG. 2	Series 416...003	Standoff Height = 8,0		
	416-XX-2	-41-003000		
	Specify number of pins	04-64		
FIG. 3	Series 416...007	Standoff Height = 10,21		
	416-XX-2	-41-007000		
	Specify number of pins	04-64		
FIG. 4	Series 416...008	Standoff Height = 11,99		
	416-XX-2	-41-008000		
	Specify number of pins	04-64		
FIG. 5	Series 416...001	Standoff Height = 15,09		
	416-XX-2	-41-001000		
	Specify number of pins	04-64		
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264				
SPECIFY PLATING CODE XX=				
Sleeve (Pin)	91	93	41	43
Contact (Clip)	0,25µm Au	0,76µm Au	0,25µm Au	0,76µm Au