






ANSI Y14.5M-1982 APPLIES				THIRD ANGLE PROJECTION 	
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH				SCALE 2:1	
CHARACTERISTICS		ELECTRICAL DATA		DO NOT SCALE PRINT	
OPERATING FORCE-----6 - 12 LBS		CONTACT ARRANGEMENT		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ± 4° WEIGHT	
FULL OVERTRAVEL FORCE---- 30 LBS MAX		4X SPDT SILVER			
RELEASE FORCE----- 4 LBS MIN	LOAD (AMPS)	28 VDC			
		SEA LEVEL	50,000 FT		
PRETRAVEL----- .040 MAX	RESISTIVE	7	7		
DIFFERENTIAL TRAVEL----- .020 MAX	INDUCTIVE	4	2.5		
OVERTRAVEL----- .250 MIN	MOTOR	4	—		

- NOTES
- 1 - COINCIDENCE OF OPERATING AND RELEASE POINTS: .010 OF PLUNGER TRAVEL
 - 2 - CORROSION RESISTANT STEEL ENCLOSURE, PLUNGER AND BUSHING
 - 3 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
 - ∇ 4 PRINT CIRCUIT DIAGRAM, CATALOG LISTING, AND DATE CODE ON NAMEPLATE
 - ∇ 5 PLASTIC MATERIAL(S) CONFORM TO MIL-M-14 OR MIL-M-24519
 - ∇ 6 12X NO. 20 LEAD WIRES PER MIL-W- 22759/16 MARKED WITH CIRCUIT IDENTIFICATION AND WIRE GAGE (1-20, 2-20 ETC. . .) PER MIL-W- 5088
 - ∇ 7 HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805