


#### Dimension A&B



DIM A	N×5.0
DIM B	(N-1)×5.0

N=Number of contacts

Poles	A&B Tolerance
4P-8P	±0.15
9P-14P	±0.25
15P-20P	±0.35
21P-24P	±0.40



N=Number of contacts



RECOMMENDED PCB LAYOUT

SIGN	DATE	DESCRIPTION	APPROVER
△	2/10 '06	Part NO is Changed	xionghaitao
△	01/12 '07	Soldering temperature changed from 245° to 250°	Tason

#### Material

- Item① Clamp : Brass , Ni plated
- Item② Terminal screw: Steel , Zinc plating "--" slot type
- Item③ Wire guard solder pin : Brass , Tin plated
- Item④ Terminal housing : Thermoplastic (UL94V-0)

#### Electrical UL

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval Deta:


△ T2 xx 0 1 x 1 xxxx G

04	4 CONTACTS	0	Black	0000:"@Logo (Standard)	RoHS
05	5 CONTACTS	5	Green	000A:"ANYTEK"Logo	Pb<40,000ppm
...	...		(RAL 6018/T)	Any special item by	
24	24 CONTACTS	6	Blue	customer request,	
		8	Grey	please contact sales	
			(RAL 7035/D)	department.	

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN PERMISSION FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	T2 - 5.0mm series 4P-24P (Solid Block)							
PART NO.	T2xx01x1xxxxG			DWG NO.	8T20101			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Aaron 2009.11.14	xionghaitao 2006.01.23				UNIT: mm	X. ±0.50
							SCALE: NONE	X.X ±0.30
				SHEET: 01/01	REV: E		X.XX ±0.10	
							X° ±1°	