








PCB Layout(Pattern Side)



Circuit Diagram



NOTE:
Rating: DC12V 50mA
Operating Force:
 lever portion: 160 ± 50 gf
 Push portion: 260 ± 50 gf
or lever portion: 240 ± 50 gf
 Push portion: 360 ± 70 gf
Travel: 4-direction $6^\circ \pm 2^\circ$
center push 0.15 ± 0.1 mm

K1-5203U □-□□

↓
高度
H
↓
柄宽
L
↓
力度
F

PART NO	NO.1	NO.2	NO.3
NOTE	H	L	Push vigor
K1-5203UB-A4	6	1.90	260±50
K1-5203UB-B4		1.92	
K1-5203UB-C4		1.95	
K1-5203UB-D4		1.97	
K1-5203UB-E4		1.99	
K1-5203UB-A5	6	1.90	360±70
K1-5203UB-B5		1.92	
K1-5203UB-C5		1.95	
K1-5203UB-D5		1.97	
K1-5203UB-E5		1.99	
K1-5203UC-B4	7.1	1.92	260±50
K1-5203UC-B5			360±70
K1-5203UD-B5	7.8	1.92	360±70
K1-5203UE-B5	8.0	1.92	360±70
K1-5203UF-B5	9.0	1.92	360±70
K1-5203U□-□□	支持其他高度、柄宽、力度等定制		

⑦	Mylar	—	1	PTFE	—	—
⑥	Contact	—	2	F.Ag/SUS	—	—
⑤	Terminal	—	6	Phosphorous copper	Plating silver	—
④	Base	—	1	LCP	Black	
③	Cover	—	1	SUS	Plating Ni	—
②	Axle sleeve	—	1	PA6T	Black	—
①	Keystoke	—	1	PA6T	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN		LIUCAN	2023.10.30				
CHECKED					TITLE:		MULTIFUNCTIONAL SWITCHES
APPROVALS					PART NO.		K1-5203U□-□□
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
			±2'	DRAWING NO.	_____	SHEET 1 OF	

	A		NEW			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.