

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	REVISION PER EG00-2081-00 (TEXT TO ENGLISH TRANSLATED)	06-SEP-00	R.S	G.F
	D3	REVISED PER ECR-09-018681	20AUG09	VKH	RRP
	D4	ECO-19-003069	01OCT2019	RS	DR

STRIP FORM ON MIDDLE REEL (CARDBOARD REEL, DIA. ABOUT 450mm)

BANDWARE AUF MITTELSPULE (PAPPSPULE, Ø CA. 450mm)

ORDER NO. BESTELL-NR.	CROSS SECTION QUERSCHNITT		STRIP LENGTH ABISOLIER-LÄNGE /mm	TYPE AUSF?HRUNG	COLOUR FARBE	L ₁ /mm	L ₂ /mm	d ₁ /mm	s ₁ /mm	d ₂ /mm	COLOUR TYPE FARBREIHE	PACKING UNIT
	mm ²	AWG										VERPACKUNGS-EINHEIT PARTS/STÜCK REEL/SPULE
966 903-2	1.50	16	10	NORMAL NORMAL	BLACK SCHWARZ	14 ±1.5	8 ±0.4	1.7 +0.25	0.15 ±0.05	3.5 ±0.2	DIN/1	7500

1

THE AWG CROSS-SECTION CAN SLIGHT DEVIATING OF THE DIN-STANDARD CROSS-SECTION VALUES

2

RECOMMENDED STRIP LENGTH

3

MAX. INSULATION-DIA. OF WIRE: d₂ MIN.- 0.1

4

COLOUR TYPE 1: COLOUR PER TELEMECANIQUE STANDARD
COLOUR TYPE 2: COLOUR PER WEIDMÜLLER STANDARD
DIN COLOUR TYPE: COLOUR PER DIN 46228 PART 4

5

TUBULAR END-SLEEVE WITH PLASTIC SLEEVE
ACCORDING TO DIN 46228 PART 4

6

LENGTH "L1" INCLUDES MOLDING FLASH PRESENT IN THIS ZONE

1

DER AWG-QUERSCHNITT KANN VON DEN DIN-NORM QUERSCHNITTSWERTEN GERINGFÜGIG ABWEICHEN.

2

EMPFOHLENE ABISOLIERLÄNGE

3

MAX. ISOLATIONS-Ø DER LEITUNG: d₂ MIN.- 0.1

4

FARBREIHE 1: FARBEN NACH TELEMECANIQUE STANDARD
FARBREIHE 2: FARBEN NACH WEIDMÜLLER STANDARD
DIN: FARBEN NACH DIN 46228 TEIL 4

5

ADERENDHÜLSE MIT KUNSTSTOFFHÜLSE
NACH DIN 46228 TEIL 4

TOLERANCES UNLESS OTHERWISE SPECIFIED:
n. ISO 8015
n. ISO 2768 - mH -E
n. DIN 16901 - 140

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
PP/E-Cu

FINISH
Sn (SEE TABLE)

DWN
E. WERNER
29-APR-96

CHK
R.SCHMIDT
29-APR-96

APVD
G.FELDMEIER
12-SEP-00

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

CUSTOMER DRAWING

NAME
TUBULAR END-SLEEVE WITH PLASTIC SLEEVE, STRIP FORM, MIDDLE REEL
ADERENDHÜLSE MIT KUNSTSTOFFHÜLSE, BANDWARE, MITTELSPULE

SIZE
A3

CAGE CODE
00779

DRAWING NO
G-966903

RESTRICTED TO
—

SCALE
—

SHEET
1 of 1

REV
D4

PLASTIC SLEEVE
KUNSTSTOFFHÜLSE

COPPER SLEEVE
KUPFERHÜLSE

1470-19 (1/15)