







$\phi 1.45^{+0.09}_{-0.06}$

(metal-plated hole)

N=NUMBER OF POLES

Dim L	(N-1)×10.16+6.58
Dim B	(N-1)×10.16

POLES	Dim L	Dim B
1p	±0.15	±0.15
2p-4p	±0.2	±0.15
5p-7p	±0.3	±0.25
8p-10p	±0.4	±0.35
11p-12p	±0.45	±0.4

SIGN	DATE	DESCRIPTION	APPROVER
△	1/31/07	The soldering temperature from 245° to 250°	Aaron
△	05/28/13	change the structure	Da cheng
△	05/28/13	update the drawing	Da cheng
△			
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!!			

Material

- Item ① Insulator body: Thermoplastic (UL94V-0)
- Item ② Insulating cover: Thermoplastic (UL94V-0)
- Item ③ Contact pin: Brass, Tin plated
- Item ④ Wire guard: Stainless steel
- Item ⑤ Pad board: Thermoplastic (UL94V-0)

Electrical:

- Voltage rating: 250V
- Current rating: 8A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 8-9mm
- Withstanding Voltage: 15KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus
- Critical dimension: △

HM xx 60 x 1 xxxx G

△ RoHS compliant (lead<4%)
In copper Alloy

△ COLOR

No. OF POLES

01: 1 POLES

02: 2 POLES

12: 12 POLES

0000 Standard @ Logo

000A Standard ANY Logo

Any special item by customer request.

please contact sales department.

0 Black (RAL9005)

2 Red (RAL3001/D)

3 Orange(RAL2011/P)

4 Yellow(RAL1018/A)

5 Green(RAL6018/T)

6 Blue (RAL5015/A)

8 Grey(RAL7004/P)

9 White(RAL1102)

C Multiple colors

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HM10.16mm Series press fit type				DWG NO.	8HM0106			Tolerance
PART NO.	HMxx60x1xxxxG				CUST NO.				X. ±0.50
APPROVED	CHECKED	DESIGNED	DRAWN		UNIT: mm				XX ±0.30
					SCALE: NONE				XX ±0.10
					SHEET: 01/01				X° ±1°
					REV: D				