


PIN RECEPTACLES

**FOR 0,20 - 0,33 DIAMETER PINS (#04 CONTACT)
AND 0,30 - 0,43 DIAMETER PINS (#10 CONTACT)
(SEE SPECIFIC CONTACT RANGE ON PAGE 250)**

8210

8210-0-15-15-04-27-04-0


Press-fit in 0,61/0,68 stepped hole



0439

0439-0-15-15-04-27-04-0


Press-fit in 0,64 mounting hole



X464

X464-X-15-XX-10-XX-04-0

Solder mount in 0,41 min. mounting hole




Basic Part Number	Length A
0464-0	3,18
0464-1	6,35
6464-0	6,99

9225

9225-0-15-XX-10-XX-10-0


Press-fit in 1,0 mounting hole



0529

0529-0-15-XX-10-XX-10-0


Solder mount in 1,02 min. mounting hole



8947

8947-0-15-XX-10-XX-10-0


Solder mount in 1,02 min. mounting hole



4993

4993-0-15-15-10-27-10-0

Compliant press-fit in 1,04 - 1,12 Dia. mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$

RoHS-2
2011/65/EU

ORDER CODE: XXXX - X - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 5,08 μ m TIN/LEAD OVER NICKEL
- ◆ 80 5,08 μ m TIN OVER NICKEL (RoHS)
- ◆ 15 0,25 μ m GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 02 2,54 μ m TIN/LEAD OVER NICKEL
- ◆ 84 2,54 μ m TIN OVER NICKEL (RoHS)
- ◆ 27 0,76 μ m GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#04 or #10 CONTACT (DATA ON PAGE 250)
(CONTACTS #04 & #10 NOT INTERCHANGEABLE)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com