







YK 224 xx 0 x x 00G

NO. OF POLES
02: 2 POLES
03: 3 POLES
04: 4 POLES
:
30: 30 POLES

G: RoHS compliant
(lead<4%) In copper Alloy

MARK
0: "@" MARK
1: "ANY" MARK

TERMINAL & SCREW PLATED
0: TERMINAL & SCREW: G/F
1: TERMINAL: G/F, SCREW: Zinc
2: TERMINAL: Sn, SCREW: G/F
3: TERMINAL: Sn, SCREW: Zinc

SIGN	DATE	DESCRIPTION	APPROVER
△	10/20'08	Add APPROVAL: CQC	Kind
△	12/05'12	Change the screw plating specification	Jacky
△	12/05'12	Change the dimensional tolerance	Jacky
△	12/12'13	Add the view and layout	Jacky
△	12/12'13	Change the withstand voltage and current	Jacky

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

MATERIALS ELECTRICAL
RATED VOLTAGE & CURRENT: cULus CQC
250 V, 10 A / 250 V, 9 A 5
WITHSTAND VOLTAGE: AC 2000 V/Min
INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
SCREW TORQUE VALUE: 5.3 Lb-In.
WIRE RANGE: 22 - 18 AWG
1) MOLDED PARTS: Thermoplastic, UL 94 V-0 BLACK
2) TERMINAL: BRASS, 0.8t, Tin PLATED
3) TERMINAL SCREWS: STEEL, M3

△ APPROVAL:  

PART NO.:
Critical dimension: 

N = Number of poles

Dim A=Nx6.35+1.0

Dim B=(N-1)x6.35

Poles	Tol.	Dim A&B
2-5p		±0.20
6-10p		±0.25
11-16p		±0.35
17-24p		±0.40
25-30p		±0.50

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YK-224 Series							
PART NO.	YK224xx0xx00G				DWG NO.	8YK0001-224		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Jacky 2013.12.12	Jacky 2013.12.12		UNIT: mm	X. ±0.50		
					SCALE: NONE	X.X ±0.30		
				SHEET: 01/01	REV.: F	X.XX ±0.10		
						X° ±1°		