






| SIGN | DATE     | DESCRIPTION        | APPROVER |
|------|----------|--------------------|----------|
| Δ    | 07/04'13 | update the drawing | Da cheng |
| Δ    |          |                    |          |

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

### Δ Material

- Item ① Terminal housing: Thermoplastic (UL94V-0)
- Item ② Solder Pin: Brass Tin plated.
- Item ③ Spring clamp : Stainless steel
- Item ④ Terminal Cover : Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 300 V
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 14-28
- Stranded wire(AWG): 14-28
- Wire strip length: 6-7 mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus
- Critical dimension: Δ

Δ H H X X 0 0 X 0 X X X X G

Δ No. OF POLES      Δ Color      Δ RoHS compliant (lead<4%) In copper Alloy

|             |                     |                                       |
|-------------|---------------------|---------------------------------------|
| 02 2 POLES  | 0 Black (RAL9005)   | 0000 Standard @ Logo                  |
| 03 3 POLES  | 2 Red (RAL3001/D)   | 000A Standard ANY Logo                |
| ...         | 3 Orange(RAL2011/P) | Any special item by customer request, |
| 24 24 POLES | 4 Yellow(RAL1018/A) | please contact sales department.      |
|             | 5 Green(RAL6018/T)  |                                       |
|             | 6 Blue (RAL5015/A)  |                                       |
|             | 8 Grey(RAL7004/P)   |                                       |
|             | 9 White(RAL1102)    |                                       |
|             | C Multiple colors   |                                       |

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

| POLES   | Dim L | Dim B |
|---------|-------|-------|
| 2p-6p   | ±0.2  | ±0.15 |
| 7p-12p  | ±0.3  | ±0.25 |
| 13p-18p | ±0.4  | ±0.35 |
| 19p-24p | ±0.45 | ±0.4  |

| TITLE    | HH - 5.0mm Series |            |          | DWG NO.    | 8HH001 | Tolerance |       |
|----------|-------------------|------------|----------|------------|--------|-----------|-------|
| PART NO. | HHxx00xxxxxG      |            |          | CUST NO.   |        | X.        | ±0.50 |
| APPROVED | CHECKED           | DESIGNED   | DRAWN    |            |        | X X       | ±0.30 |
|          | Da cheng          | 2013.07.04 | Da cheng | 2013.07.04 |        | X.XX      | ±0.10 |
|          |                   |            |          |            |        | X°        | ±1°   |