



D




C




B

A


- INSULATION RANGE: 1.09-2.79 [.043-.110]
WIRE RANGE: 0.2-0.9 mm (24-18 AWG).
- 0.00203 [.000080] MIN BRIGHT TIN-LEAD OVER
0.00127 [.000050] MIN NICKEL.
- DIMENSIONS IN BRACKETS ARE IN INCHES.
- THIS IS A RESTRICTED PRODUCT.
- THIS PRODUCT CONTAINS A CUSTOMER SPECIFIED LUBRICANT. TYCO ELECTRONICS HAS NOT EVALUATED THIS LUBE FOR USE WITH THIS CONTACT. THE CUSTOMER ASSUMES ALL RESPONSIBILITY FOR EVALUATING AND APPROVING THIS LUBRICANT IN THEIR APPLICATION.
- 0.00203 [.000080] MIN MATTE TIN OVER
0.00127 [.000050] MIN NICKEL.
- OBSOLETE PARTS



SECTION A-A
ROTATED 90° CCW



SECTION B-B



SECTION C-C

6	3-647449-1
2	647449-1
FINISH	PART NO

7

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. McEACHIN 24-AUG-2000	TE Connectivity Ltd.	
DIMENSIONS: INCHES		CHK J. ELLIS 25-AUG-2000	NAME SL-156, HOODED RECEPTACLE CONTACT, SPECIAL	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. ELLIS 25-AUG-2000	PRODUCT SPEC	
0 PLC ± -		APPLICATION SPEC		SIZE
1 PLC ± -		WEIGHT		CAGE CODE
2 PLC ± -		CUSTOMER DRAWING		DRAWING NO
3 PLC ± .005		SCALE 10:1		SHEET 1 OF 1
4 PLC ± -		REV D1		REV
ANGLES ± -				
FINISH				