




Technical specification:


Rated voltage: IEC 61076-2-101	60 V
Current rating: IEC 61076-2-101	4A bei 40°C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 65, in mated condition
Temperature range: IEC 60664-1	-30°C ... +85°C
Mating cycles: IEC 60512-9a	>=100

Materials:


Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	PBT GF, UL 94
Sealing:	FPM
Body:	Thermoplastic Elastomer, RAL 9004

Installation specification:


Recommended torque:	0,6 Nm
---------------------	--------



4x Inductance 110nH



Part no:	Description:
43-11210	SAL - 12B - RS5 - RK5 - RS5

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: a 24.08.11 VF Ä3941 data sheet revised			 dim. in mm		title: Junction box, Profibus DP, M12x1	
				date	name		
	tolerance of cable:			drawn	30.10.07	Mankopf	dwg no: 43K1A563
				appd.	30.10.07	Fromm	
	general tolerance:					part no: see table	
	0 ± 0,50mm						
0,0 ± 0,25mm							
0,00 ± 0,10mm							
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH							