




DUAL-IN-LINE SOCKETS

SERIES 214 • SURFACE MOUNT, AUTO PLACEMENT, STUB TAIL • CLOSED FRAME



- Unique floating contacts compensate for the effects of unevenly screened solder paste
- Available packaged in tubes or on tape & reel per EIA-481
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details
- Series 214 uses MM #1434 pins. See page 162 for details
- High temp. Nylon 46 insulator is suitable for all surface mount soldering processes. Closed frame insulator is vision system compatible
- For Electrical, Mechanical and Environmental Data, see page 264 for details



Total number of pins				Quantity per tube	ORDERING INFORMATION						
	A	B	C		Tube Packaging	Tape & Reel Packaging	Tape Width (mm)	QTY per Reel			
6 8 14 16 18 20	7,6 10,1 17,7 20,3 22,8 25,3	7,62 7,62 7,62 7,62 7,62 7,62	10,1 10,1 10,1 10,1 10,1 10,1	67 50 28 25 22 20	VACUUM PAD TOP SURFACE ONLY						
					214-XX-306-01-670800	214-XX-306-01-670799	16	750			
					214-XX-308-01-670800	214-XX-308-01-670799	16	1000			
					214-XX-314-01-670800	214-XX-314-01-670799	32	750			
					214-XX-316-01-670800	214-XX-316-01-670799	32	750			
					214-XX-318-01-670800	214-XX-318-01-670799	44	750			
					214-XX-320-01-670800	214-XX-320-01-670799	44	750			
					VACUUM PAD TOP AND BOTTOM						
					214-XX-624-01-670800	214-XX-624-01-670799	44	400			
					214-XX-628-01-670800	214-XX-628-01-670799	56	400			
214-XX-632-01-670800	214-XX-632-01-670799	56	400								
214-XX-640-01-670800	NOT AVAILABLE										
24 28 32 40	30,4 35,5 40,6 50,8	15,24 15,24 15,24 15,24	17,7 17,7 17,7 17,7	16 14 12 10							
					XX=Plating Code See Below		RoHS-2 2011/65/EU				
SPECIFY PLATING CODE XX =								99			44 
Sleeve (Pin) 								5,08µm Sn/Pb			5,08µm Sn
Contact (Clip) 								2,54µm Sn/Pb			2,54µm Sn