





Dimension A&B

DIM A	N×5.08
DIM B	(N-1)×5.08



N=Number of contacts

Poles	A&B Tolerance
2P-8P	±0.15
9P-14P	±0.25
15P-20P	±0.35
21P-24P	±0.40



N=Number of contacts

P.C.B LAYOUT



SIGN	DATE	DESCRIPTION	APPROVER
△	01/18/07	Soldering temperature changed from 245° to 250°	Tason
△	01/18/07	Part NO is Changed	Tason
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item 1 Terminal housing :Thermoplastic (UL 94V-0)
- Item 2 Clamp : Brass ,Ni plated
- Item 3 Wire guard solder pin : Brass ,Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- △ ● Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus

△ YM xx 41 x 0 xxxx G

04 2×2 CONTACTS
06 2×3 CONTACTS
... ..
48 2×24 CONTACTS

0 Black
5 Green
6 Blue
8 Grey

0000:"@Logo (Standard) Pb < 40,000ppm
000A:"ANYTEK"Logo (RoHS)
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YM-5.08mm -L Series				Part Name: Part No: Part Rev: Part Desc: Part Qty				
PART NO.	YMxx41x0xxxxG				DWG NO.	8YM0101			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance		
		Aaron 2009.11.30	熊海霖 2007.01.25				UNIT: mm	X.	±0.50
							SCALE: NONE	X.X	±0.30
					REV.: D	X.XX	±0.10		
				SHEET: 01/01			X°	±1°	