







N= Number of poles
Dimension Dim A. B .C

Dim A	(N+2)×10.0+2.0
Dim B	(N+1)×10.0
Dim C	(N-1)×10.0

Poles	Tolerance
2P-5P	±0.20
6P-10P	±0.25
11P-16P	±0.35
17P-24P	±0.40
25P-30P	±0.50



SIGN	DATE	DESCRIPTION	APPROVER
△	4/10'03	Dimension changed from 10.2 to 12.0	DAWN
△	2/04'06	Part No. changed	Tony
△	08/05'10	The shape of digging hole is Changed	Aaron
△	11/20'12	Change the screw plating specification	Guoxue
△	11/20'12	Change the dimensional tolerance	Guoxue
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

MATERIALS ELECTRICAL

RATED VOLTAGE & CURRENT:

300 V, 25 A

WITHSTAND VOLTAGE:

AC 2000 V/Min

INSULATION RESISTANCE:

1000 MΩ OR MORE AT DC 500 V

OPERATING TEMPERATURE RANG:

-40 °C ~ +115 °C

SCREW TORQUE VALUE:

8.8 Lb-In.

WIRE RANGE:

22 - 12 AWG

1) MOLDED PARTS:

THERMOPLASTIC, UL 94 V-0 BLACK

2) TERMINAL:

BRASS, 0.8t, Tin PLATED

3) TERMINAL SCREWS:

STEEL, M3.5

APPROVAL:

Critical dimension:

△ PART NO.:

YK 613 xx 3 x x 00G

RoHS compliant
(lead<4%)
In copper Alloy

NO. OF POLES

02: 2 POLES

03: 3 POLES

04: 4 POLES

...

30: 30 POLES

MARK

0: "@" MARK

1: "ANY" MARK

TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F

△1: TERMINAL: G/F, SCREW: ZINC

2: TERMINAL: Sn, SCREW: G/F

△3: TERMINAL: Sn, SCREW: ZINC

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-613 With Flange Series				
PART NO.	YK613xx3xx00G			DWG NO.	8YK0001-613	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
		Guoxue 2012.12.01	Guoxue 2012.12.01		UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30
						X.XX ±0.10
						X° ±1°
SHEET: 01/01		REV.: E				