







N = Number of poles

Dim L = N x 5.0

Dim P = (N - 1) x 5.0

Dim B = N x 5.0 + 1.5

	Dim L	Dim P	Dim B
2-6p	±0.20	±0.20	±0.20
7-12p	±0.25	±0.25	±0.25
13-18p	±0.30	±0.30	±0.30
19-24p	±0.40	±0.40	±0.40



P.C.B LAYOUT

SIGN	DATE	DESCRIPTION	APPROVER
△	2011.07.13	DWG NO is changed from 8T40301 to 8T40501	Chen Bo
△	2011.07.13	Add the tolerance table	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item 1 Terminal housing Thermoplastic (UL94V-0)
- Item 2 Terminal screw Steel Zinc plating "+/-" slot type
- Item 3 Terminal body Brass stamping clamp, Tin plated
- Item 4 Wire guard Stainless steel

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-20
- Stranded wire(AWG): 11-20
- Torque(Lb-In): 3.5
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C ± 10°C / 5 Sec
- Safety Approval Data:
- Critical dimension:

T4 xx 04 x x xxxx G		RoHS
Solid block		Pb<40,000ppm
02 2 CONTACTS		0000 Standard @ Logo
03 3 CONTACTS		000A Standard ANY Logo
... ..		Any special item by
24 24 CONTACTS		customer request,
Color		please contact sales
0 Black (RAL9005)		department.
5 Green (RAL6018/T)		
6 Blue (RAL5015/A)		
8 Grey (RAL7035/P)		

DIM C Length
2 4.4mm
(Connector though type)
3 3.0mm
(Connector though type)

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	T4-5.0mm Solid block Connector though type				DWG NO.	8T40501	△
PART NO.	T4xx04xxxxxxG				CUST NO.		
APPROVED	CHECKED	DESIGNED	DRAWN	Tolerance			
			Chen Bo		UNIT: mm	X.	±0.50
			2011.07.13			X.X	±0.30
						X.XX	±0.10
					SCALE: NONE	X°	±1°
					SHEET: 01/01	REV.: C	