






Δ
 $N = \text{Number of Poles}$
 $\text{Dim. } P = (N-1) \times 7.62$
 $\text{Dim. } L = (N-1) \times 7.62 + 6.08$

Poles Dim.	2P-6P	7P-12P	12P-16P
Dim.L	± 0.25	± 0.30	± 0.40
Dim.P	± 0.25	± 0.30	± 0.35

PCB. LAYOUT
Top view

SIGN	DATE	DESCRIPTION	APPROVER
	10/30/09	The dimension changed from 19.1 to 19.1±0.50	Kind
	10/30/09	Add tolerance table for Dim.L and Dim.P	Kind
	10/30/09	Terminal lever material changed to thermoplastic (UL94-HB)	Kind
	04/23/13	Update the drawing	Da cheng

Material

- | | |
|----------------------------|---|
| ● Item 1 Solder pin : | Brass , Tin plated |
| ● Item 2 Wire guard : | Stainless steel |
| ● Item 3 Terminal housing: | Thermoplastic (UL94V-0) |
| ● Item 4 Terminal cover: | Thermoplastic (UL94V-0) |
| ⚠ Item 5 Terminal lever: | Thermoplastic (UL94V-HB) |
| ● Item 6 Terminal pad: | Thermoplastic (UL94V-0) |
| Electrical | cULus |
| ● Voltage rating: | 300V |
| ● Current rating: | 15A |
| ● Wire range: | |
| ● Solid wire(AWG): | 12-28 |
| ● Stranded wire(AWG): | 12-28 |
| ● Wire strip length: | 6-7mm |
| ● Withstanding Voltage: | 1.6KV |
| ● Operating temperature: | -40°C to +115°C |
| ⚠ ● Soldering temperature: | 260°C±5°C/5 Sec |
| ● Safety Approval: |  |
| ⚠ ● Critical dimension: |  |

HT xx 50 x 0 xxxx G

→ **4** G: RoHS compliant
(lead<4%)
In copper Alloy

02	2 CONTACTS
03	3 CONTACTS
...	...
16	16 CONTACTS

 Color

- 0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7004/P)
9 White(RAL1102)
C Multiple colors

000 0 Standard @ Logo
000 A Standard ANY Logo
009 1 Standard ANY Logo
Any special item by
customer request,
please contact sales
department.

C Multiple colors

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HT-7.62 Series					
PART NO.		HTxx50x0xxxxG		DWG NO.		8HT0301	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
			Da cheng 2013.04.23	Da cheng 2013.04.23		UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
					SHEET: 01/01	REV: D	X.XX ±0.10
							X° ±1°