

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOCAD

DIST00

REV

DATE

BY

APP

DESCRIPTION

DATE

BY

APP

SEE SHEET 1

—

—

—

△ ₆	101.19 [3.984]	99.06 [3.900]	39	80	9—146509—0
△ ₆	98.65 [3.884]	96.52 [3.800]	38	78	8—146509—9
△ ₆	96.11 [3.784]	93.98 [3.700]	37	76	8—146509—8
△ ₆	93.57 [3.684]	91.44 [3.600]	36	74	8—146509—7
△ ₆	91.03 [3.584]	88.90 [3.500]	35	72	8—146509—6
△ ₆	88.49 [3.484]	86.36 [3.400]	34	70	8—146509—5
△ ₆	85.95 [3.384]	83.82 [3.300]	33	68	8—146509—4
△ ₆	83.41 [3.284]	81.28 [3.200]	32	66	8—146509—3
△ ₆	80.87 [3.184]	78.74 [3.100]	31	64	8—146509—2
△ ₆	78.33 [3.084]	76.20 [3.000]	30	62	8—146509—1
△ ₆	75.79 [2.984]	73.66 [2.900]	29	60	8—146509—0
△ ₆	73.25 [2.884]	71.12 [2.800]	28	58	7—146509—9
△ ₆	70.71 [2.784]	68.58 [2.700]	27	56	7—146509—8
△ ₆	68.17 [2.684]	66.04 [2.600]	26	54	7—146509—7
△ ₆	65.63 [2.584]	63.50 [2.500]	25	52	7—146509—6
△ ₆	63.09 [2.484]	60.96 [2.400]	24	50	7—146509—5
△ ₆	60.55 [2.384]	58.42 [2.300]	23	48	7—146509—4
△ ₆	58.01 [2.284]	55.88 [2.200]	22	46	7—146509—3
△ ₆	55.47 [2.184]	53.34 [2.100]	21	44	7—146509—2
△ ₆	52.93 [2.084]	50.80 [2.000]	20	42	7—146509—1
△ ₆	50.39 [1.984]	48.26 [1.900]	19	40	7—146509—0
△ ₆	47.85 [1.884]	45.72 [1.800]	18	38	6—146509—9
△ ₆	45.31 [1.784]	43.18 [1.700]	17	36	6—146509—8
△ ₆	42.77 [1.684]	40.64 [1.600]	16	34	6—146509—7
△ ₆	40.23 [1.584]	38.10 [1.500]	15	32	6—146509—6
△ ₆	37.69 [1.484]	35.56 [1.400]	14	30	6—146509—5
△ ₆	35.15 [1.384]	33.02 [1.300]	13	28	6—146509—4
△ ₆	32.61 [1.284]	30.48 [1.200]	12	26	6—146509—3
△ ₆	30.07 [1.184]	27.94 [1.100]	11	24	6—146509—2
△ ₆	27.53 [1.084]	25.40 [1.000]	10	22	6—146509—1
△ ₆	24.99 [.984]	22.86 [.900]	9	20	6—146509—0
△ ₆	22.45 [.884]	20.32 [.800]	8	18	5—146509—9
△ ₆	19.91 [.784]	17.78 [.700]	7	16	5—146509—8
△ ₆	17.37 [.684]	15.24 [.600]	6	14	5—146509—7
△ ₆	14.83 [.584]	12.70 [.500]	5	12	5—146509—6
△ ₆	12.29 [.484]	10.16 [.400]	4	10	5—146509—5
△ ₆	9.75 [.384]	7.62 [.300]	3	8	5—146509—4
△ ₆	7.21 [.284]	5.08 [.200]	2	6	5—146509—3
△ ₆	4.67 [.184]	2.54 [.100]	1	4	5—146509—2
△ ₆	2.13 [.084]	—	—	2	5—146509—1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

△ ₅	101.19 [3.984]	99.06 [3.900]	39	80	4—146509—0
△ ₅	98.65 [3.884]	96.52 [3.800]	38	78	3—146509—9
△ ₅	96.11 [3.784]	93.98 [3.700]	37	76	3—146509—8
△ ₅	93.57 [3.684]	91.44 [3.600]	36	74	3—146509—7
△ ₅	91.03 [3.584]	88.90 [3.500]	35	72	3—146509—6
△ ₅	88.49 [3.484]	86.36 [3.400]	34	70	3—146509—5
△ ₅	85.95 [3.384]	83.82 [3.300]	33	68	3—146509—4
△ ₅	83.41 [3.284]	81.28 [3.200]	32	66	3—146509—3
△ ₅	80.87 [3.184]	78.74 [3.100]	31	64	3—146509—2
△ ₅	78.33 [3.084]	76.20 [3.000]	30	62	3—146509—1
△ ₅	75.79 [2.984]	73.66 [2.900]	29	60	3—146509—0
△ ₅	73.25 [2.884]	71.12 [2.800]	28	58	2—146509—9
△ ₅	70.71 [2.784]	68.58 [2.700]	27	56	2—146509—8
△ ₅	68.17 [2.684]	66.04 [2.600]	26	54	2—146509—7
△ ₅	65.63 [2.584]	63.50 [2.500]	25	52	2—146509—6
△ ₅	63.09 [2.484]	60.96 [2.400]	24	50	2—146509—5
△ ₅	60.55 [2.384]	58.42 [2.300]	23	48	2—146509—4
△ ₅	58.01 [2.284]	55.88 [2.200]	22	46	2—146509—3
△ ₅	55.47 [2.184]	53.34 [2.100]	21	44	2—146509—2
△ ₅	52.93 [2.084]	50.80 [2.000]	20	42	2—146509—1
△ ₅	50.39 [1.984]	48.26 [1.900]	19	40	2—146509—0
△ ₅	47.85 [1.884]	45.72 [1.800]	18	38	1—146509—9
△ ₅	45.31 [1.784]	43.18 [1.700]	17	36	1—146509—8
△ ₅	42.77 [1.684]	40.64 [1.600]	16	34	1—146509—7
△ ₅	40.23 [1.584]	38.10 [1.500]	15	32	1—146509—6
△ ₅	37.69 [1.484]	35.56 [1.400]	14	30	1—146509—5
△ ₅	35.15 [1.384]	33.02 [1.300]	13	28	1—146509—4
△ ₅	32.61 [1.284]	30.48 [1.200]	12	26	1—146509—3
△ ₅	30.07 [1.184]	27.94 [1.100]	11	24	1—146509—2
△ ₅	27.53 [1.084]	25.40 [1.000]	10	22	1—146509—1
△ ₅	24.99 [.984]	22.86 [.900]	9	20	1—146509—0
△ ₅	22.45 [.884]	20.32 [.800]	8	18	146509—9
△ ₅	19.91 [.784]	17.78 [.700]	7	16	146509—8
△ ₅	17.37 [.684]	15.24 [.600]	6	14	146509—7
△ ₅	14.83 [.584]	12.70 [.500]	5	12	146509—6
△ ₅	12.29 [.484]	10.16 [.400]	4	10	146509—5
△ ₅	9.75 [.384]	7.62 [.300]	3	8	146509—4
△ ₅	7.21 [.284]	5.08 [.200]	2	6	146509—3
△ ₅	4.67 [.184]	2.54 [.100]	1	4	146509—2
△ ₅	2.13 [.084]	—	—	2	146509—1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC ± —

1 PLC ± 0.5[.02]

2 PLC ± 0.13[.005]

3 PLC ± —

4 PLC ± —

ANGLES ± —

FINISH

SEE TABLE

DATE

19OCT2006

CHK

J. GESFORD

DATE

19OCT2006

APVD

J. GESFORD

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

DWN

R. BROWN

19OCT2006

NAME

HEADER ASSEMBLY, MOD II,
STACKING, DOUBLE ROW,
.025 SQ.POST, UNSHROUDED

SIZE

A1

CAGE CODE

00779

DRAWING NO

146509

RESTRICTED TO

—

SCALE

4:1

SHEET

2

OF

2

REV

A1

TE Connectivity

4805 (3/11)