



Printed: Sep 23, 2011

PRODUCT NUMBER	SERIES NAME	PITCH
20020013-CXXXXXXLF	03-350	3.50 mm







N = Number of poles
 Dim A = $N \times 3.5 [0.138] + 0.80 [0.031]$
 Dim B = $(N-1) \times 3.5 [0.138]$

Poles	Tolerance
2-4p	$\pm 0.10 [0.004]$
5-7p	$\pm 0.15 [0.006]$
8-12p	$\pm 0.20 [0.008]$
13-18p	$\pm 0.25 [0.010]$
19-24p	$\pm 0.30 [0.012]$

2p to 6p with wedge, above 7p
 without wedge (including 7p)

mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
D				angles	X.±0.5 X.X±0.3 X.XX±0.1	scale	TERMINAL BLOCK PLUGGABLE, PLUG, SIGNAL, W/O FLANGE FRONT SCREW
				dr	WENDY CHEN 051810		sheet 2 of 5 size
				enr	JASON HSU 051810		20020013 A4
				chr	GARY HSIEH 051810		
				appd	JOSEPH HSIA 051810		
sheet index	revision sheet						type CUSTOMER Drawing

PRODUCT NUMBER	SERIES NAME	PITCH
20020013-DXXXXXL	03-381	3.81 mm






N = Number of poles
 Dim A = $N \times 3.81 [.150] + 0.80 [.031]$
 Dim B = $(N-1) \times 3.81 [.150]$

Poles	Tolerance
2-6p	$\pm 0.15 [.006]$
7-12p	$\pm 0.20 [.008]$
13-17p	$\pm 0.25 [.010]$
18-24p	$\pm 0.30 [.012]$


mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title TERMINAL BLOCK PLUGGABLE, PLUG, SIGNAL, W/O FLANGE FRONT SCREW			
D				angles X°±1°	linear X.X±0.5 X.X±0.3 X.XX±0.1	scale	sheet 3 of 5 size			
		dr	WENDY CHEN	051810			A4			
		enr	JASON HSU	051810			20020013			
		chr	GARY HSIEH	051810			type			
		appd	JOSEPH HSIA	051810			CUSTOMER Drawing			
sheet index	revision sheet									

PRODUCT NUMBER	SERIES NAME	PITCH
20020013-GXXXXXXLF	03-500	5.00 mm




N = Number of poles
Dim A = $N \times 5.0$ [.197]
Dim B = $(N-1) \times 5.0$ [.197]

Poles	Tolerance
2-7p	± 0.15 [.006]
8-12p	± 0.25 [.010]
13-18p	± 0.30 [.012]
19-24p	± 0.40 [.016]






mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK							
ltr	ecn	no	dr	date		tolerances unless otherwise specified				title							
D						angles 100° 100°	X.±0.5		MM [INCH]	TERMINAL BLOCK							
							X.X±0.3			PLUGGABLE, PLUG, SIGNAL, W/O FLANGE							
							X'±1"			X.XX±0.1		FRONT SCREW					
						dr	WENDY CHEN	051810		dwg no				sheet 4 of 5		size	
						engr	JASON HSU	051810		20020013				A4			
						chr	GARY HSIEH	051810									
						appd	JOSEPH HSIA	051810									
sheet index		revision sheet								type						CUSTOMER Drawing	

PRODUCT NUMBER	SERIES NAME	PITCH
20020013-HXXXXXXLF	03-508	5.08 mm



N = Number of poles
Dim A = $N \times 5.08$ [.200]
Dim B = $(N-1) \times 5.08$ [.200]

Poles	Tolerance
2-6p	± 0.15 [.006]
7-12p	± 0.25 [.010]
13-18p	± 0.30 [.012]
19-24p	± 0.40 [.016]



mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK					
ltr	ecn	no	dr	date		tolerances unless otherwise specified				title TERMINAL BLOCK PLUGGABLE, PLUG, SIGNAL, W/O FLANGE FRONT SCREW					
D						angles		MM [INCH]							
						X.±0.5									
						X.X±0.3									
						X.XX±0.1									
				dr	WENDY CHEN	051810					dwg no		sheet 5 of 5	size	
				engr	JASON HSU	051810					20020013		A4		
				chr	GARY HSIEH	051810									
				appd	JOSEPH HSIA	051810									
sheet index	revision sheet									type CUSTOMER Drawing					