




PCB Layout(Top View)



Dimension A&B&C	
DIM A	(N+2)×9.5+2.0
DIM B	(N-1)×9.5
DIM C	N×9.5+2.0

N=Number of contacts

DimensionA&B&C	Tolerance
>6~30	±0.30
>30~120	±0.40
>120~400	±0.60

SIGN	DATE	DESCRIPTION	APPROVER
△	10/14/08	將Body底部方槽改為φ3.0圓孔形	Kind
△	09/05/26	Voltage & Current changed from 300V,25A to 300V,30A	Eris
△	09/05/26	wire range changed from 22-14 AWG to 10-22 AWG	Eris
△	09/05/26	add Safety Approval	Eris
△	10/22'12	Change the screw plating specification	Jacky
△	10/22'12	Add the view	Jacky
△	10/22'12	Change the dimensional tolerance	Jacky
△	10/22'12	Change the electrical specification	Jacky
△	10/22'12	Add the dimensional label	Jacky
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

△ MATERIALS ELECTRICAL

△ RATED VOLTAGE & CURRENT:

300 V, 25A

WITHSTAND VOLTAGE:

AC 2000 V/Min

INSULATION RESISTANCE:

1000 MΩ OR MORE AT DC 500 V

OPERATING TEMPERATURE RANG:

-40 °C ~ +115 °C

SCREW TORQUE VALUE:

8.8 Lb-In.

△ WIRE RANGE:

14-22 AWG

1) MOLDED PARTS:

Thermoplastic, UL 94 V-0 BLACK

2) TERMINAL:

BRASS, 0.8t, Tin PLATED

△ 3) TERMINAL SCREWS:

STEEL, M3.5

△ APPROVAL: (c)us PENDING

PART NO.:

Critical dimension: ▽

YK 516 xx 3 x x 00G

NO. OF POLES

02: 2 POLES

03: 3 POLES

04: 4 POLES

:

:

30: 30 POLES

G:RoHS compliant(lead<4%)
in copper alloy

MARK

0: "@" MARK

1: "ANY" MARK

TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F

△ 1: TERMINAL: G/F, SCREW: Zinc

2: TERMINAL: Sn, SCREW: G/F

△ 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-516 W/Flange Series			
PART NO.	YK516xx3xx00G	DWG NO.	8YK0002-516		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Jacky 2012.10.22	Jacky 2012.10.22		X. ±0.50
					X.X ±0.30
					X.XX ±0.10
					X° ±1°