


DO NOT SCALE

DIMENSIONS IN mm

METRIC


THIRD ANGLE

PROJECTION




NOTES:

- ① FOR USE ON MINIATURE APPLICATORS (LEFT-RIGHT FEED)
AND STANDARD APPLICATORS (RIGHT-LEFT FEED).
- ② BRASS ACC ASTM B36 ALLOY 260.
- ③ PH.BRONZE ACC ASTM B103.
- ④ GAGE 0,71 MUST NOT ENTER ; GAGE 0,51 MUST ENTER.
- ⑤ REELED WITH PAPER COVER
- ⑥ **OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI**



SECTION A-A SECTION B-B

DIRECTION OFF TOP OF REEL



Terminal "U" down.

GENERAL TOLERANCES ± 0.3

⑥ OBSOLETE	①③	PRE-TINPLATED	PH.BRONZE	6-160860-8
	①②	PRE-TINPLATED	BRASS	6-160860-7
	①③	TINPLATED	PH.BRONZE	160860-4
	①③	UNPLATED	PH.BRONZE	160860-3
	①②	TINPLATED	BRASS	160860-2
	①②	UNPLATED	BRASS	160860-1
NOTES		FINISH	MATERIAL	PARTNUMBER

CUSTOMER DRAWING FOR REFERENCE ONLY
WILL NOT BE UPDATEDTHIS DRAWING IS UNPUBLISHED
RELEASED FOR PUBLICATION

TE Connectivity

NAME

.250 SRS FASTIN-ON
RECEPTACLE

D2	REVISED PER ECO-11-005140		RK	HMR	01APR11
LTR.	REVISION RECORD		DR.	CHK.	DATE
DR.:	P.BEIJNON	CHK.:	A.BIJNEN	APP.:	L.v.SOEST
DATE:	14-03-90	DATE:	-	DATE:	18-04-90

DWG.No.

160860

REV.LTR.

D2

SHEET

1 OF 1

A3