





FEMALE

A04	A05	A08	D04	B05

NOTE:

MATERIAL

M12 INSULATOR
CONTACT
NUT

PA66, UL94V-0, BLACK
GOLD FLASH PLATED BRASS
NICKEL PLATED BRASS

ELECTRICAL

RATED CURRENT
VOLTAGE
INSULATOR RESISTANCE
CONTACT RESISTANCE
MATING CYCLES

2A(8P) / 4A(4/5P)
30V(8P) / 60V(5P) / 250V(4P)
100 MOhms MIN.
10 mOhms MAX.
100 CYCLES MIN

ENVIRONMENT

OPERATION TEMPERATURE
IP RATING

-40°C TO +85°C
IP66

RECOMMENDED TORQUE

0.4Nm TO 0.8Nm

SERIES 858FYYY-203RAU1
858F = M12 FIELD INSTALLABLE
CONTACT ARRANGEMENT YYY
A04 = 4P A-CODE
A05 = 5P A-CODE
A08 = 8P A-CODE
D04 = 4P D-CODE
B05 = 5P B-CODE
GENDER 2
2 = FEMALE
CABLE OD A
A = 4mm-6mm OD
CONTACT PLATING 1
1 = GOLD FLASH

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

J. KADEL

DATE:

02/04/2022

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET OF
1 1

REV
0

DWG NO.

858FYYY-203RAU1