






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-18-016412	12OCT2018	JM	RB
	A1	REV PER ECO-18-016694	18OCT2018	JM	RB



- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY
- 2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)
- 3 MATERIAL: SILICONE
COLOR: RUST
4. RECOMMENDED WIRE DIAMETER RANGE IS 1.30 TO 2.54mm.
5. RECOMMENDED BACKSHELLS:
- STRAIGHT EXIT
A. 2292865-1 SMOOTH WIRE EXIT
B. 2292865-2 NC20/NWI7 CONDUIT WIRE EXIT
C. 2292865-3 NCI6/NWI3 CONDUIT WIRE EXIT
- 90° EXIT
D. 2302486-1 SMOOTH WIRE EXIT
E. 2302486-2 NC20/NWI7 CONDUIT WIRE EXIT
F. 2302486-3 NCI6/NWI3 CONDUIT WIRE EXIT
6. RECOMMENDED SEAL PLUG: 776363-1
7. MATING CONNECTOR: 2320937-X.

D	ORANGE	23209131-4
C	PURPLE	2320931-3
B	BLUE	2320931-2
A	TAN	2320931-1
KEY	TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J MCNEAL 20MAR2018	TE Connectivity			
		CHK R BALTER 20MAR2018				
		APVD R BALTER 20MAR2018	NAME			
DIMENSIONS:		PRODUCT SPEC	CAP ASSEMBLY, 12 POSITION, REDUCED DIA SEAL, HIGH TEMP, AMPSEAL 16			
mm		108-2184				
		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO			
		114-13065	A2 - C-2320931			
MATERIAL		WEIGHT	SCALE 3:1 SHEET 1 OF 1 REV A1			
		22.5±1g				
		Customer Drawing				