



P. C. B LAYOUT

TECHNICAL REQUIREMENT
1. MAIN TECHNICAL INDEX

- 1) CONTACT RATING: 24V/0.5A
 - 2) IMPEDANCE: 75 Ω
 - 3) INSULATION RESISTANCE: $\geq 500M \Omega$
 - 4) INSERTION FORCE:: $\leq 3.0KG/F$
WITHDRAWAL FORCE: $\geq 0.1KG/F$
 - 5) TORQUE:: 3.5N/m
 - 6) DIELECTRIC WITHSTANDING VOLTAGE: 500V/60SEC
 - 7) DURABILITY: 500CYCLES
 - 8) RESISTANCE TO SOLDERING HEAT
MANUAL WEIDING:: 3s $\pm$ 0.5s 350°C $\pm$ 5°C
AUTOMATIC: 3s $\pm$ 0.5s 260°C $\pm$ 5°C
 - 9) OPERATING TEMPERATURE: -40~85°C
2. THE PRODUCT REQUIRES THE SUFACE TO BE SMOOTH 、 CLEAN, AND MAY NOT BE DISTORTED
3. NO SCRATCHES ON THE SURFACE OF THE PRODUCT
4. THE EDGE OF THE PRODUCT CAN NOT HAVE FLASH
5. NO DIMENSION TOLERANCES ARE SHOWN IN THE FOLLOWING TABLE

4	PIN	1	COPPER ALLOY		T=0.3
3	FRAME	1	SPCC	-	T=0.4
2	HOUSING	1	PBT	-	WHITE
1	THREAD HEAD	1	ZINC ALLOY	NI PLATED	
NO.	PART NAME	QTY	MATERIAL:	PLATING	REMARK

浙江富港电子有限公司					
DRAWN	LPJ	DATE	19. 08. 26	 	
CHECKED	—	DATE	—		
APPROVE	LGB	DATE	19. 08. 26	PROPORTION	WEIGHT
				IF-08B-7.2	