



DIT IS ONZE EIGENDOM EN MAG NOCH NAGEMAAKT, HERDRUKT, OVERGEMAAKT AAN DERDEN, NOCH VOOR FABRIKATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE TOELATING. BIJ NIET GEBRUIK IS DE TERUGZENDING VERPLICHT.

THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY. NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO US IN CASE OF NO USAGE

00

BS, A , 202361, 004

REV.	DATE	DESCRIPTION	BY	C 'K' 'D'
00	16/11/07	FIRST ISSUE	R.Ch	



Catalog Number	Dimension				
	A ±0.2	B ±0.15	C ±0.15	D ±0.2	E max
UTG6187SN	34.3	24.0	22.5	19.1	33.0
UTG6187PN	34.3	24.0	22.5	19.1	29.0

MATERIAL :


- BODY : GLASS-FILLED POLYESTER.
COLOUR : BLACK.
- BAYONET RING : HIGH STRENGTH CuZn ALLOY,NICKEL PLATED.

PERFORMANCE CHARACTERISTICS :

- OPERATING TEMPERATURE : -55 °C TO +125 °C.
- INSULATION RESISTANCE : 5000 M Ohm MIN.
- TEST POTENTIAL : 2000 V EFF.
- DESIGN : ACCORDING TO VDE 0110 GROUP C/380V.

NOTES :

- 1 CONNECTOR ACCEPTS # 16 STRIP FORMED, MACHINED AND SUBMINIATURE COAXIAL PIN AND SOCKET CONTACTS.
- 2 CONTACTS TO BE ORDERED SEPARATELY : REFER TO DRAWINGS BSA 060291, BSA 060101, BSA 060152.

GEN. ST.	01	02	03	04	05	06	07	08	0D	50	60	70	80	90																	
INT. ST.	10	11	12	13	14	18	20	31	32	33	34	38	39	40	42	43	44	45	46	48	56	70	72	73	75	76	81	82	83	84	88
1DEC ±0,2 1DEC 2DEC ±0,1 2DEC ANGLES ±1° HOEKEN			APPR.			DATE			SIGN.			UTG BANTAM SIZE 18-7 PLUG																			
WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE.			DRAFT			16/11/07			ROUILLARD Ch			CAT. No. UTG6187-N																			
			CHECKED									 SOURIAU Connection Technology SOURIAU Route Nationale 23 72470 CHAMPAGNE SCALE 1 : 1																			
			PROD. MGR.																												
ALL DIMENSIONS IN MM 			PR.ENG.MGR.									BS, A , 202361, 004 DRAWING NR. CUSTOMER DRAWING REVISION																			
			PR.MGT.MGR.																												
ALLE AFMETINGEN IN MM			REFERENCES / REFERENTIES												NOT EXPORT CONTROLLED																