


PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
B	DCN 54127	04/24	SEE PDM



MATERIAL:	
BODY, INSERT, & CLAMP NUT:	STAINLESS STEEL PER AMS-5640, ALLOY UNS S30300, TYPE 1
FERRULE & CONTACT:	BERYLLIUM COPPER PER ASTM B196, ALLOY No. UNS C17300, TD04
INSULATOR:	POLYETHERIMIDE RESIN (ULTEM 1000) PER ASTM D5205.
FINISH:	
BODY, INSERT & CLAMP NUT:	PASSIVATED PER AMS-2700.
FERRULE & CONTACT:	GOLD PER ASTM B488, TYPE II, CODE C, CLASS 1.27, OVER NICKEL PER AMS-QQ-N-290, CLASS 1, .000050" MIN.
PERFORMANCE:	
IMPEDANCE:	50 OHMS
FREQ. RANGE:	DC TO 65.0 GHz

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:  FRACTIONAL: $\pm 1/64$ ANGULAR: X° $\pm 1^{\circ}0'$ 
-----------	-----------	--