



P.C.B LAYOUT
TOP VIEW



POLE	2	3	4	5	6	7	8	9	10	11	12
Dim L	15.00	22.50	30.00	37.50	45.00	52.50	60.00	67.50	75.00	82.50	90.00
Dim P	7.50	15.00	22.50	30.00	37.50	45.00	52.50	60.00	67.50	75.00	82.50
Tol.	±0.20			±0.25				±0.35			

SIGN	DATE	DESCRIPTION	APPROVER
△	01/12/07	Part NO. is Changed	Tason
△	01/12/07	Soldering temperature changed from 245°C to 250°C	Tason
△	3/2/09	Operating temperature changed (-40°C to +115°C)	Tony
△	3/2/09	Add "VDE" Safety Approval	Tony
△	9/28/09	Dimension is changed from 3.80mm to 3.50mm.	Aaron
△	10/09/13	update the drawing	Guoxue
△	10/09/13	Soldering temperature is changed from 250°C ±10°C/5 Sec to 260°C ±5°C/5 Sec	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ① Terminal housing: Thermoplastic (UL 94V-0)
- Item ② Clamp: Brass, Ni plated
- Item ③ Wire guard solder pin: Brass, Tin plated.
- Item ④ Terminal screw: Steel, Zinc plating "-" slot type
- △ Electrical: UL VDE CQC
- Voltage rating: 300V 450V 450V
- Current rating: 10A 10A 24A
- Wire range: 0.34-4.0 mm² 0.2-2.5 mm²
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 3.5Lb-In 0.4 Nm 0.4 Nm
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV 2.5KV 2.5KV
- △ ● Operating temperature: -40°C to +115°C
- △ △ ● Soldering temperature: 260°C ±5°C/5 Sec
- △ △ ● Safety Approval:

● Critical dimension:

△ TI xx 21 x 0 xxxx G

02 2 POLES
03 3 POLES
...
12 12 POLES

COLOR
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange (RAL2011/P)
4 Yellow (RAL1018/A)
5 Green (RAL6018/T)
6 Blue (RAL5015/A)
8 Grey (RAL7035/D)
9 White (RAL1102)
C Green (RAL6018/U)

0000: "Logo (Standard)
000A: "ANYTEK" Logo
Any special item by
customer request,
please contact sales
department.

RoHS compliant
(lead < 4%)
In copper Alloy

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TI 7.5 SERIES 2P-12P "-" screw (Stackable)						
PART NO.	TIxx21x0xxxxG			DWG NO.	8TI0101		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Guoxue 2013.10.09	Guoxue 2013.10.09			UNIT: mm	X. ±0.50
				SHEET: 01/01		SCALE: NONE	X.X ±0.30
						REV.: G	X.XX ±0.10
							X° ±1°