






D

C

B

A



- 1 NYLON, UL 94V-0 RATED, BLACK.
- 2 STAINLESS STEEL.
- 3 BRASS.
- 4 CONTACT BODY: 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END. GOLD FLASH ON REMAINDER, BOTH OVER 1.27um [.000050] MIN NICKEL. CONTACT POST: 2.54um [.000100] MIN TIN-LEAD OVER 1.27um [.000050] MIN NICKEL.
- 5 RECOMMENDED PC BOARD HOLE SIZE FOR CONTACT POST = 1.02±0.08[.040±.003] DIA.
- 6 CONTACT BODY: 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END. GOLD FLASH ON REMAINDER, BOTH OVER 1.27um [.000050] MIN NICKEL. CONTACT POST: 2.54um [.000100] MIN TIN OVER 1.27um [.000050] MIN NICKEL.

6	5.59[.220]	213854-4
6	10.90[.429]	213854-3
4	5.59[.220]	213854-2
4	10.90[.429]	213854-1
FINISH	DIM A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN D.HARDY 01-03-95	TE Connectivity	
DIMENSIONS: mm [INCHES]	CHK R.STONE 01-09-95	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T.COULSON 01-10-95	PRODUCT SPEC	
0 PLC ± -	PRODUCT SPEC	108-10024	
1 PLC ± -	APPLICATION SPEC	-	
2 PLC ± -	SIZE	CAGE CODE	DRAWING NO
3 PLC ± .005	WEIGHT	A1	00779
4 PLC ± -	CUSTOMER DRAWING	SCALE	2:1
ANGLES ± -	SHEET	1	OF 1
FINISH	REV	G1	