


JMC P/N	CAPACITANCE	Q @ 100 MHz	COLOR CODE
2320-0SL	0.6 TO 2.5 pF	> 3000	RED
2320-1SL	1.0 TO 5.0 pF	> 1000	BLACK
2320-2SL	2.5 TO 10 pF	> 1000	BLUE
2320-3SL	5.0 TO 18 pF	> 500	GREEN
2320-4SL	6.5 TO 25 pF	> 300	AMBER



MI DRG. NO.	2320SLK	REV.
2320SL		K
CERA-TRIM® CAPACITOR		

SPECIFICATIONS	FILE: THINOUT
CAPACITY RANGE	SEE TABLE
WORKING VOLTAGE	250 VDC (TEST VOLTAGE 500 VDC)
Q @ 100 MHz	SEE TABLE
INSULATION RESISTANCE	> 10 ⁴ MEGOHMS
TEMPERATURE RANGE	-55°C TO +125°C
TORQUE	0.05 TO 1.0 OZ. IN.
MOISTURE RESISTANCE	MIL-STD-202, METHOD 106
SHOCK	100 g @ 6 ms
VIBRATION	15 g @ 10-2000 Hz
SETTING DRIFT	< 1%
CERAMIC DIELECTRIC STRUCTURE	
SOLDER FINISH TERMINALS	

K	01/13/14	SSH	MAI	MAI	001202
J	10/08/10	NK	MAI	MAI	000870
H	01/02/07	MLD	MAI	MAI	000479
G	05/19/06	MLD	MAI	MAI	000398
F	10/09/02	MLD	MAI	TAM	020-089
E	09/30/02	MLD	TAM	TAM	020-085
D	03/16/00	-	-	-	000-108
LEVEL	DATE	DRN.	CHK.	APP.	ECN

REVISIONS

DRN.	CHK.	APP.	SCALE
TAM	TAM	JHT	4" = 1"
DATE	DATE	DATE	.XX ± .015
03/16/00	03/16/00	03/16/00	.XXX ± .005



JOHANSON MANUFACTURING CORPORATION
 ROCKAWAY VALLEY ROAD, BOONTON, N.J. 07005 (973)334-2676 FAX (973)334-2954
 ELECTRONIC ACCURACY THROUGH MECHANICAL PRECISION

PROPRIETARY INFORMATION CONTAINED NOT TO BE USED WITHOUT JOHANSON MANUFACTURING CORPORATION APPROVAL