




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	REVISED PER ECR-16-011494	26JUN2017	NK	CX
	A3	ECO-19-006934	10MAY2019	AP	WS
	A4	REVISED PER ECN-22-179646	02NOV2022	WLS	VS
	A5	REVISED PER ECN-23-242776	14DEC2023	WLS	VS



- ① MATERIAL: HOUSING - UL 94V-O RATED HIGH TEMP NYLON, COLOR BLACK.
CONTACTS - BRASS
HOLDDOWNS: - PHOSPHOR BRONZE.
- ② RECOMMENDED PC BOARD THICKNESS OF 1.57.
- ③ PLATING: CONTACTS - 0.38 μ m MINIMUM GOLD ON MATING AREA,
2.54 μ m MINIMUM MATTE TIN ON SOLDER TAILS,
ALL OVER 1.27 μ m MINIMUM NICKEL.
HOLDDOWNS: 2.54 μ m MINIMUM MATTE TIN OVER 1.27 μ m MINIMUM NICKEL.
- 4 COUNTERPART RECOMMENDED IS PN 1445022 OR 2008571 (DASH ACC. TO NUMBER OF POSITION).
- 5 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

OBSOLETE	—33.00	37.43	33.00	40.14	12	3-1445088-2—
OBSOLETE	—30.00	34.43	30.00	37.14	11	3-1445088-1—
OBSOLETE	27.00	31.43	27.00	34.14	10	3-1445088-0
	24.00	28.43	24.00	31.14	9	2-1445088-9
	21.00	25.43	21.00	28.14	8	2-1445088-8
	—18.00	22.43	18.00	25.14	7	2-1445088-7—
	15.00	19.43	15.00	22.14	6	2-1445088-6
	12.00	16.43	12.00	19.14	5	2-1445088-5
	9.00	13.43	9.00	16.14	4	2-1445088-4
	6.00	10.43	6.00	13.14	3	2-1445088-3
	3.00	7.43	3.00	10.14	2	2-1445088-2
		DIM Z	DIM V	DIM T	DIM W	NO. OF POS'N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09OCT2000 J.ROOT CHK 17-APR-2001 K. WHITAKER APVD 17-APR-2001 C. JONES		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.20 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1°		NAME RT ANG THRU HOLE HEADER ASSY, 0.38 MIC GOLD CONTACTS W/THRU HOLE HOLDDOWNS, SGL ROW, MICRO MATE-N-LOK™	
		PRODUCT SPEC 108-1836 APPLICATION SPEC 114-13000		SIZE A2	CAGE CODE 00779
MATERIAL 		FINISH 		DRAWING NO C=1445088	
		WEIGHT -		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 2
				REV A5	

