


N=NUMBER OF CONTACTS



RECOMMENDED PCB LAYOUT

	Dim A	Dim B
2-6p	± 0.15	± 0.10
7-12p	± 0.20	± 0.20
13-18p	± 0.30	± 0.25
19-24p	± 0.40	± 0.30

N = Number of poles
Dim A=Nx5.08
Dim B=(N-1)x5.08

SIGN	DATE	DESCRIPTION	APPROVER
△	02/09'06	Part No. is changed.	Marvin
△	06/23'06	Touque standard is changed from 3.5 Lb-In to 2.6 Lb-In	Marvin
△	06/23'06	Added cULus logo	Marvin
△	04/03'10	Part No. is changed.	Tason

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Terminal body (metal housing): Brass(CuZn)
- Terminal screw: Steel Zinc plating “-” slot type
- Wire guard: Stainless steel
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 15A
- Wire range:
 - Solid wire(AWG): 14-22
 - Stranded wire(AWG): 14-22
- Torque: 2.6Lb-In
- Screw: M2.6
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:  CE, RoHS

TC xx 2 3 x x xxxx G

POLES COLOR DIM C Length

02 02 CONTACTS	0 BLACK	0	4.4mm
03 03 CONTACTS	5 GREEN(RAL6018/T)	1	3.8mm
...	6 BLUE	2	3.5mm
24 24 CONTACTS			

000 0 Standard
Any special item by
customer request,
please contact sales
department.

ANYTEK				CUSTOMER COPY			
				ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD.			
TITLE		TC-5.08 Series 2-Interlock					
PART NO.		TCxx23xxxxxG△		DWG NO.	8TC0603		
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
		Tason 2010.04.03	Tason 2010.04.03	 	UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
				SHEET: 01/01	REV.: B	X.XX ±0.10	
						X° ±1°	