









版数 VER.	年月日 DATE	CN NO.	変更内容 DESCRIPTION	製図 DR.	担当 CHK.	承認 APPD.	承認 APPD.
2	21/SEP/2018	026677	CORRECT AN ERROR AND ADD A NOTE.		Y. YOKOYAMA	—	Y. SAITOU



APPEARANCE (REF.)
(5 : 1)



APPLICABLE P.C.B DIMENSION (REF.)
(10 : 1)

[TABLE-1]

FIRST DIGIT		SECOND DIGIT		THIRD DIGIT		FOURTH, FIFTH DIGIT		SIXTH DIGIT	
SUPPLIER	MARKING	YEAR	MARKING	MONTH	MARKING	DAY	MARKING	LINE CODE	MARKING
JAE	J	2018	8	1	1	1	01	1	1
		2019	9	2	2	2	02	2	2
		2020	0	3	3	3	03	3	3
		2021	1	4	4	4	04	4	4
		2022	2	5	5	5	05	5	5
		2023	3	6	6	6	06	6	6
		2024	4	7	7	7	07	7	7
		2025	5	8	8	8	08	8	8
		2026	6	9	9	9	09	9	9
		2027	7	10	10	10	10	10	A
				11	X	11	11	11	B
				12	Y			12	C
								13	D
								30	30
								31	31






TABLE 2

Pin No.	A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
	GND	TX1+	TX1-	V _{BUS}	CC1	D+	D-	SBU1	V _{BUS}	RX2-	RX2+	GND
Pin No.	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
	GND	RX1+	RX1-	V _{BUS}	SBU2	D-	D+	CC2	V _{BUS}	TX2-	TX2+	GND

- NOTE 1. CO-PLANARITY
SMT TERMINAL OF CONTACT AND MID PLATE: 0.08 MAX.
NOTE 2. PRODUCTION LOT NUMBER IS MARKED AS INDICATED. LOT NUMBER CONTENTS REFER TO TABLE-1.
NOTE 3. VACUUM AREA.
NOTE 4. METAL EXPOSED AREA SIZE COULD BE SLIGHTLY CHANGED BASED ON MOLDING PROCESS CONDITION IN EACH LOT, HOWEVER THIS WOULD NOT AFFECT CONNECTOR FUNCTION.
NOTE 5. THE SHELL LENGTH IS LESS THAN THE MINIMUM REFERENCED IN THE USB TYPE C STANDARD. AS SUCH THE SYSTEM IMPLEMENTER IS RESPONSIBLE FOR ACHIEVING PRODUCT RELIABILITY, THAT THE CONNECTOR BE MOUNTED SUCH THAT ALL FUNCTIONAL USB REQUIREMENTS ARE MET.
NOTE 6. THERE IS A POSSIBILITY OF BURR OR PELLICLE OCCUR AT LIM PART, BUT IT HAS NO IMPACT FOR ITS PRODUCTION ABILITY, ASSEMBLY AND WATERPROOF ABILITY.
NOTE 7. NO PCB ROUTING ALLOWED IN THIS AREA.
NOTE 8. LASER WELD POINTS MAY BE DISCOLORED.
NOTE 9. IN ORDER TO PREVENT DAMAGE AND SECURE LEAKAGE, THE CONNECTOR SHOULD BE PROTECTED WITH CASE.
NOTE 10. REFER TO TABLE 2 FOR PIN ASSIGNMENT (FRONT VIEW).
NOTE 11. MATING DIMENSIONS CONSIST OF "Universal Serial Bus Type-C Cable and Connector Specification".

9	POTTING	1	—	—	COLOR: BLACK
8	GASKET	1	SILICONE RUBBER	—	COLOR: BLACK
7	INSULATOR	1	HEAT RESISTING PLASTICS	—	COLOR: BLACK
6	INNER PLATE	1	STAINLESS STEEL	—	—
5	SHELL	1	STAINLESS STEEL	—	—
4	BRACKET	1	STAINLESS STEEL	NICKEL PLATING	—
3	MID PLATE	1	STAINLESS STEEL	NICKEL PLATING	—
2	CONTACT B	12	COPPER ALLOY	CONTACT AREA AND SOLDER TAILS: GOLD OVER NICKEL	CONTACT AREA: NICKEL: 1 μm MIN. Au: 0.1 μm MIN.
1	CONTACT A	12	COPPER ALLOY	CONTACT AREA AND SOLDER TAILS: GOLD OVER NICKEL	SOLDER TAILS: NICKEL: 1 μm MIN. Au: 0.03 μm MIN.

符号 NO.	名 称	個 数	材 料	仕 上 FINISH	備 考 REMARKS
仕様書 (SPECIFICATION) JACS-30353-24					
第1版 (ORIGINAL DATE) 11/SEP/2018			シリーズ (SERIES) DX07		
一般公差 (GENERAL TOLERANCE)			名称 (TITLE) DX07WH24JA3		
寸法 (DIMENSION)			質量 (MASS)		
± 0.8			単位 (UNIT): mm		
× ± 0.4			図面番号 (DRAWING NO.) SJ120981		
× ± 0.1			版数 (VER.) 2		
× ±			JAE Connector DIV. Proprietary. Copyright (C) 2018, Japan Aviation Electronics Industry, LTD.		