







△ N=NUMBER OF POLES

Dim L	(N-1)×7.5+6.50
Dim B	(N-1)×7.5



SIGN	DATE	DESCRIPTION	APPROVER
△	1/31/07	The soldering temperature from 24.5° to 250°	Aaron
△	05/28/13	change the structure	Da cheng
△	05/28/13	update the drawing	Da cheng
△			
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item ① Insulator body: Thermoplastic (UL94V-0)
- Item ② Insulating cover :Thermoplastic (UL94V-0)
- Item ③ Contact pin : Brass, Tin plated
- Item ④ Wire guard: Stainless steel
- Item ⑤ Pad board: Thermoplastic (UL94V-0)

Electrical:

- Voltage rating: 250V
- Current rating: 8A
- Wire range:

- Solid wire(AWG): 12-28

- Stranded wire(AWG): 12-28

- Wire strip length: 8-9mm

- Withstanding Voltage: 1.5KV

- Operating temperature: -40°C to +115°C

- Soldering temperature: 260°C±5°C/5 Sec

- Safety Approval:

- Critical dimension:

HM xx 90 X 0 xxxx G

No. OF POLES ———→ △ RoHS compliant (lead<4%) In copper Alloy

01: 1 POLES ———→ △ COLOR 0 Black (RAL9005) 0000 Standard @ Logo
02: 2 POLES ———→ 2 Red (RAL3001/D) 000A Standard ANY Logo

3 Orange(RAL2011/P) Any special item by customer request,
4 Yellow(RAL1018/A) please contact sales department.
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7004/P)
9 White(RAL1102)
C Multiple colors

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HM 7.5mm Series Dip solder		DWG NO.	8HM0003		Tolerance
PART NO.	HMxx90x0xxxxG					X. ±0.50 XX ±0.30 XXX ±0.10 X° ±°
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	UNIT: mm SCALE: NONE	
	Da cheng 2013.05.28	Da cheng 2013.05.28			SHEET: 01/01 REV: F	