






REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN17A0069~80	2017-10-12	Lingpeng	Add The Label And Change The Title
C	NI80019	2019-03-02	Peng	Add 5Pin
D	C230889	2023/06/15	He long	△*1



ALTW
CONFIDENTIAL
2019-03-02
R&D DEPT.

⑥ Connector










UNIT:mm		TITLE	△ UL11 Cable Joiner Screw-in Type		
TOLERANCE	±0.5mm	SCALE	1:1	SIZE	A4
		REV.	D	WC-REV.	.0
				QC	Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DWG NO	CUSTOMER	DRAWN BY	CHECKED BY	APPROVED BY	DATE
	SC-L-UL11-XX-XX	ALTW	Peng	MaFei	Jerry	2019-03-02
						2019-03-02
						2019-03-02

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

	1	2	3	4	5	6	7	8
F								
E	QTY: 1PCS →		QTY: 120PCS →				9 Carton	
D	SC-L-ULII-XX-XX L: Cable Joiner Type: ULII		Seal's Color: BL-Blue(藍色) For Cable Range: Ø4.5~Ø6.5mm YW-Yellow(黃色) For Cable Range: Ø6.5~Ø8.5mm GN-Green(綠色) For Cable Range: Ø8.5~Ø10.5mm RD-Red(紅色) For Cable Range: Ø10.5~Ø12.5mm AA-All Seals For Cable Range: Ø4.5~Ø12.5mm					
C			No. of Conductor: 02-2Poles 03-3Poles 04-4Poles 05-5Poles					
B	Pole Assignments Front View							
			2 Pole		3 Pole		4 Pole	
					5 Pole			
A	UNIT:mm TOLERANCE ±0.5mm		TITLE ULII Cable Joiner Screw-in Type SCALE 1:1 REV. D		SIZE A4 WC-REV. .0 SHEET 2 OF 2 QC: Inspection item		Amphenol LTW 安費諾亮泰企業股份有限公司	
					ITEM NO DWG NO SC-L-ULII-XX-XX CUSTOMER ALTW		DRAWN BY Peng CHECKED BY MaFei APPROVED BY Jerry DATE 2019-03-02 DATE 2019-03-02 DATE 2019-03-02	
							8 W10814-03-0001A2	

Both A Unassembled product And An Instruction Are In A PE Bag.
(將一套未組裝的產品和說明書, 放置於一個PE袋, 並封口)

- Note: 
- *  Important Dimension To Check.
 - * Waterproof Rate: IP68 (50M, 24H)
 - * Housing: PA66+GF, Black.
 - * Gland Nut: PA66, Black.
 - * Gland Pipe: PA66, Black.
 - * Contact: Brass, Nickel Plated
 - * Gasket & L-Gasket : Silicone, Yellow.
 - * Seal: Silicone, Blue & Yellow & Green & Red.
 - * Rated Voltage: 2~5 Pole 600V AC
 - * Rated Current: 2~4 Pole Max. 20A
5 Pole Max. 10A
 - * Operating Temperature: -40°~+105°.
 - * Gland Pipe Recommended Tightening Torque:
8~10 Kgf.cm(0.78~0.98 N.m)
 - * Gland Nut Recommended Tightening Torque:
8~10 Kgf.cm(0.78~0.98 N.m)
 - * Seal For Cable OD: Ø4.5~Ø6.5mm, Blue.
Ø6.5~Ø8.5mm, Yellow.
Ø8.5~Ø10.5mm, Green .
Ø10.5~Ø12.5mm, Red.
 - * Screws for Wire connection recommended tightening torque: 2.00~4.50kgf.cm / 0.196~0.44 N.m
 - * Applicable Wire gauge: 2~4 Pole: 18AWG ~ 12AWG
5 Pole: 20AWG ~ 16AWG
 - * UL2238 Certification